

Drawer with partial extension for drawer cabinet, system 700

Depth 600 mm

Application:

For individual fitting of the HK cabinet housing 700 The drawers can be installed in the housing in any sequence, but the sum of the front heights must be equal to the useful height of the housing.

Execution:

- Made of sheet steel metal with a reinforced, perforated bottom (25 mm hole grid)
- Run on Delrin rollers in rails which are suspended in the housing with plug caps
- Inner sides slotted all around, for attaching and fixing insert material such as compartment rails and dividers
- Equipped with aluminium handle strip, paper and cellon strips and lateral cover caps
- SOFT-CLOSE-AUTOMATIC for smooth and silent drawer closing, see no. 50392 005.



Art. no.	50302 299
Brand	HK
Manufacturer Part Number	50302299
Drawer front height	360 mm
Drawer cabinet height	100 mm
Mount height	340 mm
Drawer width (inner dimension)	900 mm
Drawer depth (inner dimension)	600 mm
Drawer surface	0.54 m ²
Pullout type	Partial extension
Load-carrying capacity	100 kg
Drawer with slots	Yes
Perforated drawer base	Yes
Material	Sheet steel
Colour of front	Anthracite grey RAL 7016
Box colour	Light grey RAL 7035
Surface	Powder-coated
Gross Weight	17.200 kg
Product Group	5BB

EAN

4053625404582