

Combination workbench, series V 2800

Solid beechwood 2800 mm, 6 drawers with full extension



Execution:

- Solidly welded steel sheet construction
- Base with drawer block
- Base made of square-section steel tube 45 x 45 x 2 mm, with level compensation
- Delivered fully assembled
- Per workstation 3 drawers with 100% full extension, 1 x front height 60 mm, 1 x front height 90 mm, 1 x front height 120 mm



Art. no.	50303 331
Number of drawers	6 PCS
Working height	850 mm
Worktop width	2800 mm
Pullout type	Full extension
Worktop height	50 mm
Colour of front	Anthracite grey RAL 7016
Worktop depth	700 mm
Cabinet colour	Light grey RAL 7035
Adjustable in height	No
Drawer surface	0.27 m ²
Surface	Powder-coated
With single pull-out safety brake	Yes
Load-carrying capacity	800 kg
Lock type	DOM® locking system
Drawer front height	2 x 60 mm, 2 x 90 mm, 2 x 120 mm
Drawer width (inner dimension)	500 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	500 x 540 mm
Material of worktop	Solid beech
Drawer depth (inner dimension)	540 mm
Load-carrying capacity per drawer	100 kg
Material of base frame	Steel plate
Central locking	Yes
Levelling	Yes
Product Group	Prod. Gr. 502

EAN

4014641159191