

Han shielded module basic, male



Part number	09 14 027 3021
Specification	Han shielded module basic, male
HARTING eCatalogue	https://b2b.harting.com/09140273021

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Modules
Series	Han-Modular [®]
Type of module	Han [®] Shielded module basic
Size of the module	Single module
Description of the module	With 180° shielding element

Version

Termination method	Crimp termination
Gender	Male
Number of contacts	27
further contacts	+ shielding
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.09 0.52 mm²
Rated current	4 A
Rated voltage	32 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 +125 °C
Mating cycles	≥500



Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	2
Net weight	0.01 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140184985
eCl@ss	27440218 Module for industrial connectors (data)