

► Selection guide – Cable for PSENmech, PSENrope




PSENmech



PSENrope

PSENmech and PSENrope – Cable selection for connection to PDP67 F 8DI ION/PSS67



PSS67/PDP67 cable



PDP67 F 8DI ION

Type	Description
PSS67/PDP67 cable	Cable for connection to PDP67 F 8DI ION/PSS67

Type	Description
PDP67 F 8DI ION	Sensor junction box for decentralised periphery PNOZmulti



PSENmag




PSENmag

PSENmag – Cable selection for connection to any evaluation device



PSEN cable M8-4sf



PSEN cable M8-8af

Type	Description	Cable drag chain capability
4 PSEN cable M8-4sf	Cable for connection to any evaluation device	◆
4 PSEN cable M8-4af		◆
1 PSEN cable M8-8sf		
1 PSEN cable M8-8af		
2 PSEN cable M12-8sf		◆
2 PSEN cable M12-8af		◆
3 PSEN cable M12-5sf		

and PSENmag

Features	Certification	Order number (by length)				
		3 m	5 m	10 m	20 m	30 m
<ul style="list-style-type: none"> ▶ Connection 1: Open cable ▶ Connection 2: Straight, M12, 5-pin, plug 	UL	380 705	380 709	380 706	380 707	380 708



Features	Certification	Order number
Multiple interface PDP67, protection type IP67, PL e of EN ISO 13849-1, SIL CL 3 of EN/IEC 62061 and Cat. 4 of EN 954-1, M12 metal thread	TÜV, BG, UL	773 600

Features	Certification	Order number (by length)					
		2 m	3 m	5 m	10 m	20 m	30 m
<ul style="list-style-type: none"> ▶ Connection 1: Straight, M8, 4-pin, socket ▶ Connection 2: Open cable 	UL	533 111	-	533 121	533 131	-	533 141
<ul style="list-style-type: none"> ▶ Connection 1: Angled, M8, 4-pin, socket ▶ Connection 2: Open cable 	UL	533 110	-	533 120	533 130	-	533 140
<ul style="list-style-type: none"> ▶ Connection 1: Straight, M8, 8-pin, socket ▶ Connection 2: Open cable 	UL	533 150	-	533 151	533 152	533 153	533 154
<ul style="list-style-type: none"> ▶ Connection 1: Angled, M8, 8-pin, socket ▶ Connection 2: Open cable 	-	-	-	-	533 162	-	-
<ul style="list-style-type: none"> ▶ Connection 1: Straight, M12, 8-pin, socket ▶ Connection 2: Open cable 	UL	-	540 319	540 320	540 321	540 333	540 326
<ul style="list-style-type: none"> ▶ Connection 1: Angled, M12, 8-pin, socket ▶ Connection 2: Open cable 	UL	-	540 322	540 323	540 324	-	540 325
<ul style="list-style-type: none"> ▶ Connection 1: Straight, M12, 5-pin, socket ▶ Connection 2: Open cable 	UL	-	630 310	630 311	630 312	630 298	630 297