

PB 8240

Schraubenziehersätze mit Wandhalter  
Jeux de tournevis avec support mural



⊖ 8240



⊕ 8242



⊗ 8243



⊖ ⊕ 8244



⊖ ⊗ 8245



⊛ 8440

NEW DESIGN 03 / 2013

				
PB 8240	8100/1, 2, 3, 4, 5, 6	637	1	7 610733 078684
PB 8242	8190/0, 1, 2, 3	423	1	7 610733 078707
PB 8243	8192/0, 1, 2, 3	423	1	7 610733 078714
PB 8244	8100/1, 2, 3, 4; 8190/1, 2	465	1	7 610733 078721
PB 8245	8100/1, 2, 3, 4; 8192/1, 2	464	1	7 610733 078738
PB 8440	8400/8, 9, 10, 15, 20, 25	384	1	7 610733 078745

**PB 8100**

Schraubenzieher für Schlitzschrauben, parallele Spitze: optimale Kraftübertragung, kein Cam-out Effekt  
 Tournevis pour vis à fente, bout parallèle, transmission de force optimale, aucune force d'éjection (cam-out)



PB 8100.00-70	1,2	0.3	2	2.5	70	140	14	10	7 610733 089239
PB 8100.0-80	1,6	0.4	2.5	3	80	160	20	10	7 610733 078851
PB 8100.1-90	2	0.5	3.5	3.5	90	180	29	10	7 610733 078868
PB 8100.2-100	2,5	0.6	4	4	100	195	39	10	7 610733 078875
PB 8100.3-120	3	0.8	5.5	5	120	220	57	10	7 610733 078882
PB 8100.4-140	3,5	1	6.5	6	140	245	80	10	7 610733 078899
PB 8100.5-160	4-5	1.2	8	7	160	270	111	10	7 610733 078905
PB 8100.6-180	6	1.6	10	8	180	300	153	10	7 610733 078912

**PB 8190**

Kreuzschraubenzieher Phillips, Spitze nach DIN ISO 8764-1  
 Hauptabmessungen fett gedruckt  
 Tournevis en croix Phillips, pointe selon DIN ISO 8764-1  
 Dimensions principales imprimées en caractères gras



PB 8190.00-40	1-1,2	00	3	40	100	9	10	7 610733 214242
PB 8190.00-60	1-1,2	00	3	60	120	15	10	7 610733 089246
<b>PB 8190.0-60</b>	<b>1,6-2</b>	<b>0</b>	<b>4</b>	<b>60</b>	<b>140</b>	<b>23</b>	<b>10</b>	<b>7 610733 078967</b>
PB 8190.0-100	1,6-2	0	4	100	190	27	10	7 610733 216772
PB 8190.0-150	1,6-2	0	4	150	240	32	10	7 610733 216789
<b>PB 8190.1-80</b>	<b>2,5-3</b>	<b>1</b>	<b>5</b>	<b>80</b>	<b>175</b>	<b>44</b>	<b>10</b>	<b>7 610733 078974</b>
PB 8190.1-130	2,5-3	1	5	130	225	51	10	7 610733 216796
PB 8190.1-200	2,5-3	1	5	200	295	62	10	7 610733 216802
PB 8190.1-300	2,5-3	1	5	300	395	77	10	7 610733 216819
<b>PB 8190.2-100/6</b>	<b>3-5</b>	<b>2</b>	<b>6</b>	<b>100</b>	<b>205</b>	<b>72</b>	<b>10</b>	<b>7 610733 078981</b>
PB 8190.2-150/6	3-5	2	6	150	255	83	10	7 610733 204472
PB 8190.2-200/7	3-5	2	7	200	310	127	10	7 610733 212620
PB 8190.2-250/7	3-5	2	7	250	360	141	10	7 610733 212637
PB 8190.2-300/7	3-5	2	7	300	410	156	10	7 610733 212644
PB 8190.2-400/7	3-5	2	7	400	510	186	10	7 610733 216826
<b>PB 8190.3-150</b>	<b>6-8</b>	<b>3</b>	<b>8</b>	<b>150</b>	<b>270</b>	<b>146</b>	<b>10</b>	<b>7 610733 078998</b>
PB 8190.3-200	6-8	3	8	200	320	165	10	7 610733 216833
<b>PB 8190.4-200</b>	<b>8-10</b>	<b>4</b>	<b>10</b>	<b>200</b>	<b>330</b>	<b>221</b>	<b>10</b>	<b>7 610733 216840</b>

**PB 8192**

Kreuzschraubenzieher Pozidriv, Spitze nach DIN ISO 8764-1  
 Hauptabmessungen fett gedruckt  
 Tournevis en croix Pozidriv, pointe selon DIN ISO 8764-1  
 Dimensions principales imprimées en caractères gras











<b>PB 8192.0-60</b>	<b>1,6-2</b>	<b>0</b>	<b>4</b>	<b>60</b>	<b>140</b>	<b>23</b>	<b>10</b>	<b>7 610733 079032</b>
<b>PB 8192.1-80</b>	<b>2,5-3</b>	<b>1</b>	<b>5</b>	<b>80</b>	<b>175</b>	<b>44</b>	<b>10</b>	<b>7 610733 079049</b>
PB 8192.1-130	2,5-3	1	5	130	225	51	10	7 610733 216857
<b>PB 8192.2-100</b>	<b>3-5</b>	<b>2</b>	<b>6</b>	<b>100</b>	<b>205</b>	<b>72</b>	<b>10</b>	<b>7 610733 079056</b>
PB 8192.2-150	3-5	2	6	150	255	83	10	7 610733 216864
PB 8192.2-300	3-5	2	6	300	405	117	10	7 610733 216871
<b>PB 8192.3-150</b>	<b>6-8</b>	<b>3</b>	<b>8</b>	<b>150</b>	<b>270</b>	<b>146</b>	<b>10</b>	<b>7 610733 079063</b>
<b>PB 8192.4-200</b>	<b>8-10</b>	<b>4</b>	<b>10</b>	<b>200</b>	<b>330</b>	<b>221</b>	<b>10</b>	<b>7 610733 216888</b>

## PB 8400

Schraubenzieher für Torx®-Schrauben, SwissGrip Griff, Grössen 27 - 40 mit Sechskantansatz  
 Tournevis pour vis Torx®, manche SwissGrip, grandeurs 27 - 40 avec prise 6 pans



								
PB 8400.3-40	1	2.5	40	117		13	10	7 610733 089345
PB 8400.4-40	1	2.5	40	117		13	10	7 610733 089352
PB 8400.5-50	1,6	3	50	127		14	10	7 610733 089369
PB 8400.6-50	2	3	50	127		15	10	7 610733 084692
PB 8400.7-50	2	3	50	127		15	10	7 610733 089376
PB 8400.8-60	2,5	3	60	140		20	10	7 610733 079209
PB 8400.9-60	2,5	3.5	60	140		22	10	7 610733 079216
PB 8400.10-70	3	3.5	70	160		28	10	7 610733 079223
PB 8400.15-80	3,5	4	80	175		38	10	7 610733 079230
PB 8400.20-100	4	5	100	200		54	10	7 610733 079247
PB 8400.25-120	5	6	120	225		77	10	7 610733 079254
PB 8400.27-125	5-6	6	125	230	10	82	10	7 610733 079261
PB 8400.30-130	6	7	130	240	10	110	10	7 610733 079278
PB 8400.40-140	8	8	140	260	13	152	10	7 610733 079285