

MILAN S.r.l. a socio unico

**Head Office – Export department:**  
 Viale Europa, 74  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.4556-4158  
 F. +39 02 9039.4551  
 www.taskercables.com

**Ufficio Commerciale e Centro Distribuzione**  
 Viale Europa 72 Strada F12  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.0037-0059  
 F. +39 02 9039.0049  
 www.tasker.it

## Technical Datasheet



# tasker® RG 59 BU 75 Ω Coaxial Mil. C 17 F Standard Cable



A		B		C		D
---	--	---	--	---	--	---

**CATEGORY** Coaxial cable 75 Ω (See Video Catalogue)

- A:** Black Soft **PVC** Sheath. - Outer Diam. Ø 6,10 (±0,20) mm.
- B:** Shielding O.F.C. red copper Braid covering 98%.
- C:** Core Insulation with transparent compact PE - Nom. Ø 3,70 (±0,20) mm
- D:** Stiff Wire in CW - 1x0,58 mm – Nom. Cross section 1x0,26 mm<sup>2</sup>

**MARKING**  
**CUSTOM**

**tasker®** RG59 75 Ohm Mil.- C17/F Coaxial Video Cable Italy  
 This product is also available in other 8 different versions, among which **L.S.Z.H., PE, PUR**, with or without **Steel Armor**

### Cable Properties

<b>Conductor Resistance</b>	158 Ω/Km ± 5%
<b>Capacity Core/Shield</b>	67 pF/mt
<b>Velocity of Propagation</b>	66%
<b>Impedance</b>	75 Ω ± 3%
<b>Max Rated Voltage</b>	2.000 V
<b>Operative Temperature</b>	-15/+70°C

### Attenuation dB/100 mt.

<b>50 MHz</b>	7,4
<b>100 MHz</b>	10,7
<b>200 MHz</b>	15,7
<b>400 MHz</b>	22,7
<b>800 MHz</b>	33,6
<b>1000 MHz</b>	38,0

<b>USE</b>	<input checked="" type="checkbox"/>	Indoor	Interno Edificio
<b>Impiego</b>	<input checked="" type="checkbox"/>	Outdoor Limited	Esterno Limitato
		Outdoor Direct Burial	Esterno Interrato
		.....	.....

<b>INSTALLATION</b>	<input checked="" type="checkbox"/>	Fixed	Fissa
<b>Posa</b>	<input checked="" type="checkbox"/>	Flexible Limited	Flessibilità limitata
	<input checked="" type="checkbox"/>	Dynamic (Drag Chain)	Mobile in Catena
		Dynamic (Torsion)	Mobile in Torsione

<b>INFORMATION</b>	<input checked="" type="checkbox"/>	RoHS2 Compliant
<b>Informazioni</b>	<input checked="" type="checkbox"/>	Ver. D /27.06.16
		.....