
7528

ORIGINAL | Lamps with metal bases



Product benefits

- Wide product range
- Reliable quality

Product features

- Original spare parts

Product datasheet

Technical data


Electrical data

Power input	25 / 6 W
Nominal voltage	12.0 V
Nominal wattage	21/5 W
Power input tolerance	±6 / ±10 %
Test voltage	13.5 / 13.5 V

Photometrical data

Luminous flux	440/35 lm
Luminous flux tolerance	±15 / ±20 %

Dimensions & weight



Length	52.5 mm
Diameter	26.5 mm
Product weight	10.50 g

Lifespan

Lifespan B3	180 / 1250 h ¹⁾
Lifespan Tc	290 / 4000 h ¹⁾

¹⁾ Filament 1 / Filament 2

Additional product data

Base (standard designation)	BAY15d
-----------------------------	--------

Certificates & standards

ECE category	P21/5W
Approval marks – approval	E1 approval

Product datasheet

Country specific categorizations

Order reference	7528 21/5W 12V
------------------------	----------------

Country specific information

Product code	METEL code	SEG number	STK number	UK Org
4050300838069	OSRA7528	8328084	-	-
4050300925523	OSRA7528BLI2	-	4730331	-

Product datasheet

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4050300838069	7528	Unpacked 1	68 mm x 31 mm x 33 mm	0.07 dm ³	28.83 g
4050300525129	7528	Folding carton box 10	58 mm x 54 mm x 139 mm	0.44 dm ³	125.50 g
4008321091055	7528	Shipping carton box 50	283 mm x - x 72 mm	3.02 dm ³	714.50 g
4050300925523	7528	Blister 2	95 mm x 70 mm x 18 mm	0.12 dm ³	21.20 g
4008321140548	7528	Shipping carton box 20	280 mm x - x 80 mm	2.31 dm ³	314.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.