

## 2.54mm PCB connectors

Order code	Manufacturer code	Description
22-2540	n/a	0.156" 10W CRIMP TERM.HOUSING (RC)
22-2515	n/a	0.156" 5W CRIMP TERM.HOUSING (RC)
22-2520	n/a	0.156" 6W CRIMP TERM.HOUSING (RC)
22-2530	n/a	0.156" 8W CRIMP TERM.HOUSING (RC)
22-2500	n/a	0.156" 2W CRIMP TERM.HOUSING (RC)
22-2505	n/a	0.156" 3W CRIMP TERM.HOUSING (RC)
22-2510	n/a	0.156" 4W CRIMP TERM.HOUSING (RC)

2.54mm PCB connectors	Page 1 of 2
The enclosed information is believed to be correct, Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 20/02/2007

## 0.156" CRIMP HOUSING




### SPECIFICATION

VOLTAGE RATING : AC, DC, 250V max

CURRENT RATING : 7A, max

APPLICABLE PC BOARD THICKNESS : .063" (1.6mm)

Material: Nylon 6/6 UL 94V-2



Circuits	Dim A	Dim B
2	3.96	8.5
3	7.92	12.5
4	11.88	16.4
5	15.84	20.4
6	19.80	24.4
8	27.72	32.3
10	35.64	40.2