


## PROFIBUS-PLUG-MALE (SUB-D) 90°

Screw terminals up to 12Mbits/s

Bus Connection Plug 90°  
SUB-D9 (male), screw terminals  
PROFIBUS

### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Technical Data

Operating voltage	via the fieldbus device; 4.75...5.25 V DC
Terminating resistor	integrated, switchable
Current consumption	max. 12.5 mA
Transfer rate	to 12 Mbit/s

#### General data

Protection	IP20
Dimensions H x W x D	64x40x17 mm
Temperature range	0...+60 °C (storage temperature -25...+80 °C)

#### Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1