

T250XL0X2



Article Number: 111-25200

Heavy Duty Cable Tie, 40.6" Long, 250 lb Tensile Strength, PA66, Black, 25/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number T250XL0X2

Type T250XL

Color Black (BK)

Features and Benefits

- Heavy duty design to offer higher tensile strength.
- Buckle feature on head allows excess strap to be tucked away after installation.

Product Description HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Heavy Duty Cable Tie, 40.6" Long, 250 lb Tensile Strength, PA66, Black, 25/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 250.0 lbs

Minimum Tensile Strength (Metric) 1115.0 N

Length L (Imperial) 40.6 "

Length L (Metric) 1030.0 mm

Fixation Method None

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.49 "

Width W (Metric) 12.5 mm

Bundle Diameter Min. (Imperial) 0.47 "

Bundle Diameter Min. (Metric) 12.0 mm

Bundle Diameter Max. (Imperial) 12.0 "

Bundle Diameter Max. (Metric) 305.0 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 25 Pieces

Carton Quantity 250

Weight (Metric) 15.436 kg

Material and Specifications

Material Polyamide 6.6 (PA66)
Material Shortcut PA66
Flammability UL94 V2
Halogenfree Yes
Operating Temperature -40°F to +185°F (-40°C to +85°C)
ROHS Compliant Yes
UL Listed (US and Canada) No
UL Recognized (US and Canada) Yes