



Avaya Wireless Conference Phone B169

The Avaya B169 Wireless Conference Phone is a breakthrough, making conference calling easier and more convenient. Take the B169 Wireless Conference Phone anywhere in the office and get the exceptional quality and wealth of features you expect from the flagship Avaya B100 Series conference phones—with a big difference: there's no need for phone jacks or power outlets. That's the freedom of the B169 Wireless Conference Phone.

Capabilities

You Can Take It with You

Why take conference calls only from specific conference rooms, boardrooms or executive suites within your facility? Simply carry the uniquely designed B169 Wireless Conference Phone anywhere in the office that has wireless access and you're good to go. Conduct high quality audio conferences virtually anytime and anywhere. The rechargeable lithium-ion battery provides superior performance for up to 60 hours of talk time; that's a full work week without having to recharge.

Crystal Clear Sound

Avaya has gone to great lengths so that the sound quality of the B169 Wireless Conference Phone lives up to the extraordinary standards of the rest of our award-winning conference phones. The B169 supports DECT, with the GAP / CAT-iq technology standard, to reduce interference from other devices and deliver clear conversations. With the award-winning Avaya OmniSound® 2.0 technology, every participant is easily heard, with noise suppression filters that virtually eliminate distracting background noise.

Good Things Come in Unique (and Wireless) Packages

Each of the Avaya B100 Series Conference Phones is packed with capabilities to make conference calling easier and more productive. The B169 Wireless Conference Phone furthers that tradition. It includes an SD card slot to record calls on-the-fly and archive them for future review. Its built-in conference guide helps you dial multi-party calls, store up to 20 call groups and initiate reoccurring conference calls.



Enjoy a New Level of Freedom and Convenience With Conference Calling

Easily expand the coverage of the B169 with available add-on microphones. Use the included phone book to conveniently store up to 200 frequently called numbers.

Benefits

Enhance Communications

Bring HD quality audio conferencing with you where and when you need it; everyone on the call (and in the room) can be heard with clarity.

Improve Productivity

Set-up and manage conference calls with ease; record calls for archiving and playback.

Make Faster Decisions

Make it easy to collaborate and communicate with colleagues, customers and suppliers by taking conference calls just about anywhere in your office.



Each of the Avaya B100 Series Conference Phones is packed with capabilities to make conference calling easier and more productive.

Specifications	
Feature	Description
Audio Features	<ul style="list-style-type: none"> ▪ OmniSound HD wideband via USB ▪ Microphone: Omni-directional, 360° ▪ Pickup range: up to 30 m2 (320 sq ft.), up to 12 persons, 20 with expansion microphones ▪ Volume: 90 dB SPL 0.5m (RMS) ▪ Frequency response: 200-7000 Hz ▪ Equalizer: soft, neutral and bright
Connections	<ul style="list-style-type: none"> ▪ Power supply: AC adapter 100-240 V AC / 14V DC ▪ Expansion microphones ▪ Mobile phone connection ▪ IP DECT SC Base Station (SIP) ▪ DECT base station: analog RJ-11
Battery	5200 mAh, up to 60 h talk time / 270 h standby
Platform Support	<ul style="list-style-type: none"> ▪ Avaya Aura® ▪ Avaya IP Office™ ▪ Avaya Approved Third Party Platforms
Directory	<ul style="list-style-type: none"> ▪ Phonebook: 200 contacts ▪ Call groups: 20 groups
Recording	Support SD memory card up to 2 GB

Each of the Avaya B100 Series Conference Phones is packed with capabilities to make conference calling easier and more productive. The B169 Wireless Conference Phone furthers that tradition.

Specifications	
Anti-theft protection	Kensington security slot
Dimension	Diameter 240 mm; Height 77 mm
Weight	2.2 lb
Color	Liquorice black
Display	Backlit monochrome LCD, 128x64
Keypad	<ul style="list-style-type: none"> ▪ Alphanumeric 0-9, *, # ▪ Off-hook, on-hook, mute, hold, volume up / down ▪ 5 button menu navigation ▪ Line mode ▪ Conference guide
Environmental Conditions	<ul style="list-style-type: none"> ▪ Temperature: +5°C to +40°C ▪ Relative humidity: 20-80% condensation free
Languages	Danish, Dutch, English, Finnish, French, German, Italian, Norwegian, Polish, Russian, Spanish, Swedish and Turkish



About Avaya

Businesses are built by the experiences they provide, and every day millions of those experiences are delivered by Avaya Holdings Corp. (NYSE: AVYA). Avaya is shaping what's next for the future of work, with innovation and partnerships that deliver game-changing business benefits. Our cloud communications solutions and multi-cloud application ecosystem power personalized, intelligent, and effortless customer and employee experiences to help achieve strategic ambitions and desired outcomes. Together, we are committed to help grow your business by delivering Experiences that Matter. Learn more at www.avaya.com.