

PRODUCT RANGE				
nps)	L(mH)	R(mOhm ) per winding		
0.5	40	2300		
1.0	18	640		
2.0	7.5	160		
3.0	3.2	71		
4.0	2.4	40		
6.0	1.4	19		
3.0	0.74	9.6		

## RATED VOLTAGE250V ACLINE FREQUENCYDC TO 440HzTEMPERATURE RANGE-25C TO + 100CAMBIENT TEMPERATURE +45C @ RATED CURRENT

				-	
	GENERAL SPECIFICATION				
	FOR CMV				
[ 1 OF 1	05,10,20,30,40,60,80				
LE 1:2	DRAWING NO.	ISSUE 05			
\3	Civity		Release		