


## Myriad Deco - Housing only

MYRIAD DECO HOUSING FLOOD 3000K PHDM EM SILVER REF  
2057975



### Product features

- The Myriad Housing 3000K Flood accent downlight is a high efficient 12W recessed spotlight, luminous flux: 1037lm, luminaire efficacy 86lm/W. Colour rendering index Ra>80, Colour temperature 3000K, Beam angle 46°, Protection rating IP20, Cut out dimensions: 76mm.



### PRODUCT OVERVIEW

Product name	MYRIAD DECO HOUSING FLOOD 3000K PHDM EM SILVER REF
Technology	LED
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Interior
General application	Museums & Galleries, Office, Retail, Residential & Consumer
ETIM Class	EC001744
Warranty	5 years
Fixture luminous flux (lm)	1037
Luminaire efficacy (lm/W)	86
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	90
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	46
Photobiological Risk Group	RG1
Luminous flux (emergency) (lm)	359
Total power consumption (W)	12
Electrical protection	Class II
Control gear type	Electronic ballast
Dimming method	Other
Minimum dimming level (%)	10
Housing colour	Silver
IP rating	IP20
IK rating	IK02
Product EAN number	5025768579754

### DATA TABLE

General data

## Myriad Deco - Housing only

*MYRIAD DECO HOUSING FLOOD 3000K PHDM EM SILVER REF*  
2057975

<b>Product name</b>	MYRIAD DECO HOUSING FLOOD 3000K PHDM EM SILVER REF
<b>Technology</b>	LED
<b>Housing</b>	Aluminium
<b>Mount</b>	Ceiling recessed mounting
<b>Environment</b>	Interior
<b>General application</b>	Museums & Galleries, Office, Retail, Residential & Consumer
<b>Performance ambient temperature Tq (°C)</b>	25
<b>ETIM Class</b>	EC001744
<b>Warranty</b>	5 years

### Optical data

<b>Fixture luminous flux (lm)</b>	1037
<b>Luminaire efficacy (lm/W)</b>	86
<b>LOR (%)</b>	100
<b>Colour temperature (K)</b>	3000
<b>Light colour</b>	Warm White
<b>CRI (Ra)</b>	90
<b>Colour Variation Initial (SDCM)</b>	SDCM3
<b>Adjustable chromaticity</b>	N
<b>Beam Angle (°)</b>	46
<b>Photobiological Risk Group</b>	RG1
<b>Luminous flux (emergency) (lm)</b>	359
<b>Emergency duration (h)</b>	3

### Electrical data

<b>Total power consumption (W)</b>	12
<b>Mains voltage (V)</b>	230-240V
<b>Electrical protection</b>	Class II
<b>Control gear type</b>	Electronic ballast
<b>Transformer required</b>	Yes
<b>Dimming method</b>	Other
<b>Minimum dimming level (%)</b>	10
<b>Drive current (mA)</b>	250
<b>Energy Efficiency Class (A-&gt;G) of contained light source</b>	E
<b>Nominal Frequency (Hz)</b>	50/60Hz

### Lifetime data

<b>Lifespan L70 B50</b>	100000
<b>Lifespan L80 B20</b>	100000
<b>Lifespan L90 B10</b>	68500

### Physical data

<b>Housing colour</b>	Silver
<b>IP rating</b>	IP20
<b>IK rating</b>	IK02
<b>Nominal Product Height (mm)</b>	72

## Myriad Deco - Housing only


### MYRIAD DECO HOUSING FLOOD 3000K PHDM EM SILVER REF 2057975

Cutout Dimensions (W x L in mm or Diameter in mm)	76
Weight (kg)	1.39
Recessed Depth (mm)	72

#### Packaging

Single packaging type	Carton
Product EAN number	5025768579754
Packaging single length / height (cm)	17.5
Packaging single width (cm)	15.0
Packaging single depth (cm)	17.5
DUN14 (outer)	05025768579754
Units per outer package	1
Packaging outer length / height (cm)	17.5
Packaging outer width (cm)	15.0
Packaging outer depth (cm)	17.5


## PHOTOMETRY



## TECHNICAL DRAWINGS

## Myriad Deco - Housing only

*MYRIAD DECO HOUSING FLOOD 3000K PHDM EM SILVER REF*  
**2057975**



Dimensions (mm)