

Inset Kit LED IP44


INSET TREND KIT SW IP44 REFLED ES50 36° WH WW DIM

3001764



Product features

- GU10 Housing with REFLED ES50 36° lamp included, Ideal for indoor application, Loop in - loop out box included



PRODUCT OVERVIEW

Product name	INSET TREND KIT SW IP44 REFLED ES50 36° WH WW DIM
Technology	LED
Cap/Base	GU10
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Residential & Consumer
ETIM Class	EC001744
E-number FI	4271315
E-number SE	7467394
Warranty	3 years
Fixture luminous flux (lm)	345
Luminaire efficacy (lm/W)	76
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Beam Angle (°)	40
Light source included	0029126
Total power consumption (W)	4.5
Control gear type	Electronic ballast
Dimming method	Mains: leading / trailing edge
Housing colour	White
IP rating	IP44/20
IK rating	IK02
Product EAN number	8711971017646

DATA TABLE

General data

Product name	INSET TREND KIT SW IP44 REFLED ES50 36° WH WW DIM
--------------	---

Inset Kit LED IP44

INSET TREND KIT SW IP44 REFLED ES50 36° WH WW DIM
3001764

Technology	LED
Cap/Base	GU10
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Residential & Consumer
ETIM Class	EC001744
E-number FI	4271315
E-number SE	7467394
Warranty	3 years

Optical data

Fixture luminous flux (lm)	345
Luminaire efficacy (lm/W)	76
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Adjustable chromaticity	N
Beam Angle (°)	40

Electrical data

Light source included	0029126
Total power consumption (W)	4.5
Mains voltage (V)	220-240V
Control gear type	Electronic ballast
Transformer required	Yes
Dimming method	Mains: leading / trailing edge
Energy Efficiency Class (A->G) of contained light source	F

Physical data

Housing colour	White
IP rating	IP44/20
IK rating	IK02
Diffuser finish	Transparent
Diffuser material	Other
Nominal Product Height (mm)	100
Nominal Product Diameter (mm)	95
Cutout Dimensions (W x L in mm or Diameter in mm)	75
Weight (kg)	0.224
Recessed Depth (mm)	140

Packaging

Single packaging type	Carton
Product EAN number	8711971017646
Packaging single length / height (cm)	13.1
Packaging single width (cm)	10.17
Packaging single depth (cm)	8.47

Inset Kit LED IP44

INSET TREND KIT SW IP44 REFLED ES50 36° WH WW DIM

3001764

DUN14 (outer)	18711971017643
Units per outer package	30
Packaging outer length / height (cm)	28.7
Packaging outer width (cm)	28.4
Packaging outer depth (cm)	53.1

PHOTOMETRY

TECHNICAL DRAWINGS

