

torque wrench

MANOSKOP® 730 Fix with calibration certificate



Application:

fixed tightening torque for increased safety in series use

Execution:

- chuck for exchangeable plug-in tools
- double stop signal
- dual scale showing Nm and ft-lb
- adjustment head can be unscrewed after adjusting the release torque
- two-component handle made from extremely resistant plastic
- ergonomically shaped, non-slip adjustment element
- QuickRelease safety catch on insert head
- low-wear triggering system with bending rod.



Art. no.	52281 410
Brand	STAH LWILLE
Manufacturer Part Number	96503010
Min. torque	20 Nm
Max. torque	100 Nm
Min./max. torque	20-100 Nm
Scale value torque	2 Nm
Insert shank square	9 x 12 mm
Length	370 mm
Error limit (%)	3 %
With scale	Yes
Calibration certificate	Yes
Gross Weight	1.800 kg
Product Group	531

EAN

4018754269440