

Li-Ion Battery H2B297

- 7.4 V, 4.6 Ah
- Integrated Protection Circuit
- Soft pack
- 10 cm wire



Specification

General	
Configuration	2S2P
Nominal voltage	7.4 V
Nominal capacity	4600 mAh
Watt-hour rating	34.04 Wh
Standard charging	8.4 V, 3.22 A, 4 h, 25°C (Constant voltage, constant current)
Standard discharging	4.6 A (Constant current, 3.0 V end, 25°C
Continuous allowable discharging current	< 3 A
Cell	
Type	Sanyo UR18650F
Typical capacity	2400 mAh
Safety protection board	
Cut off voltage	4.35 V
End of discharge voltage	2.3 V
Over current detection	5 A
Environmental	
Operating temperature range	Standard charging 0..40°C
	Standard discharging -20..60°C
Physical	
Dimensions	66x38x36 mm
Weight	0.190 kg
Connection	2 wires 10 cm

Li-Ion Battery H2B297

Dimensions

