

H510084

Exxact Transistordimmer 630W BP Vit

Partnumber: WDE008313

Wholesalernumber: 1370916

EAN 13 code: 3606480333088

Exxact dimmer electron trafo 630W white

Technical information

► **Compatibility**

product compatibility complete with Exxact frame

► **Functional**

switch function 1-pole 2-way

control type rotary push type

dimmer control rotary push type

number of loop terminals 1

protection type short-circuit and overload protection with automatic reset

► **Electrical**

rated current 10 A - 230 V AC

► **Connections**

connections - terminals screw terminals

clamping connection capacity 1 x 1.5...2 x 2.5 mm² solid cable(s)

1 x 1.5...2 x 2.5 mm² solid stranded cable(s)

► **Installation**

wiring device mounting flush

► **Product identification**

range of product Exxact

product or component type dimmer

dimmer type transistor

load type incandescent lamp: 60...630 W

halogen lamp: 60...600 W @230 V

electronic transformer: 60...630 W

colour tint white

► **Additional information**

quantity per set 1 piece

► **Physical characteristics**

shape of screw head pozidriv No 1 and combi

material ABS (acrylonitrile butadiene-styrene)

embedding depth 29 mm mm

height 87 mm mm

width 87 mm mm

projecting depth 22 mm mm

► **Environment**

IP degree of protection IP20 (also with visual parts removed)

► **Certifications and standards**

standards EN 60669-1

EN 60669-2-1

product certifications CE

FIMKO

NEMKO

SEMKO

Supplier information

Supplier: Schneider Electric Sverige AB

Fax: +46 155 26 54 91

Web: <http://www.schneider-electric.se>

Adress: Eskilstunavägen 7, 611 56 Nyköping

Phone: +46 155 26 54 00

e-Mail: info@se.schneider-electric.com