



SPARE KEY TYPE 10 FOR KEYSWITCH MOBILE PANEL,
AMOUNT AND CONTENT: SEE TECHNICAL DATA

Product type designation	
Standards, approvals, certificates	
CE mark	Yes
Ambient conditions	
Ambient temperature in operation	
• Min.	0 °C
• max.	55 °C
Storage/transport temperature	
• Min.	-20 °C
• max.	70 °C
Relative humidity	
• Operation, max.	90 %
Mechanics/material	
Material of housing	
• Sheet metal	Yes; Handle made of plastic
Dimensions	
Width	35 mm
Height	18 mm
Thickness	4 mm
Weights	
Without packaging	30 g
Scope of supply	

Delivery unit in items

10; Coupled with key ring

other

Note:

For Mobile Panel 1st Generation

Usable in the following products

- Product 1 [6AV6645-0DE01-0AX1](#)
- Product 2 [6AV6645-0EC01-0AX1](#)
- Product 3 [6AV6645-0EF01-0AX1](#)
- Product 4 [6AV6645-0FE01-0AX1](#)
- Product 5 [6AV6645-0GC01-0AX1](#)
- Product 6 [6AV6645-0GF01-0AX1](#)
- Product 7 [6AV6645-0CC01-0AX0](#)
- Product 8 [6AV6645-0AC01-0AX0](#)
- Product 9 [6AV6645-0BC01-0AX0](#)

last modified:

12.03.2015