

**M8-Round-Plug Connector, Single-Ended Cordsets,
According to IEC 61976-2-104**


RKMV | RKMVV



3-, 4-, and 8-Poles

Actuator/sensor cordset, single-ended, M8, 3-, 4-, and 8-poles, female straight connector with self-locking threaded joint and molded cable.

RKMV




*a O-Ring



Actuator/sensor cordset, single-ended, M8, 3-, 4-, and 8-poles, female 90° connector with self-locking threaded joint and molded cable.

RKMVV




*a O-Ring

Pin Assignments

M8

3 poles



- 1 = brown
- 3 = blue
- 4 = black

4 poles



- 1 = brown
- 2 = white
- 3 = blue
- 4 = black

8 poles



- 1 = white
- 2 = brown
- 3 = green
- 4 = yellow
- 5 = grey
- 6 = pink
- 7 = blue
- 8 = red



Be Certain with Belden

M8-Round-Plug Connector, Single-Ended Cordsets, According to IEC 61976-2-104

RKMV 3 | RKMV 4 | RKMV 8 | RKMWV 3 | RKMWV 4

Technical Data

Environmental

Degree of protection IP 67 / NEMA 6P
 Operating temperature range -40°C (-40°F) / +90°C (+194°F)

Mechanical

Housing / Molded body TPU
 Insert PA / TPU
 Contact CuZn, pre-nickel and 0.8 microns gold-plated
 Coupling nut CuZn, nickel-plated

Electrical data

Contact resistance ≤ 5 mΩ
 Nominal current at 40°C 4 A
 Nominal voltage 3 poles 60 V
 4 poles 30 V
 Rated voltage 3 poles 63 V
 4 poles 36 V
 Test voltage 3 poles 1.5 kV eff. / 60 s
 4 poles 0.8 kV eff. / 60 s
 Insulation resistance > 10⁹ Ω
 Pollution degree 3

Cable Specifications

Cable No.	Outer Jacket	Conductor Size	Jacket Color	OD
06	PVC	3 x 0.34 mm ²	Orange	.197" (5.0 mm)
07	PVC	4 x 0.75 mm ²	Orange	.197" (5.0 mm)
224	PUR, halogen-free	3 x 0.34 mm ²	Black	.169" (4.3 mm)
225	PUR, halogen-free	4 x 0.34 mm ²	Black	.185" (4.7 mm)
354	PUR, halogen-free	8 x 0.14 mm ²	Black	.197" (5.0 mm)

Part Number	Pins	Outer Jacket	Standard Cable Lengths	Characteristics
RKMV 3-06/...M	3	PVC	2 M / 5 M / 10 M	
RKMV 3-224/...M		PUR, halogen-free	2 M / 5 M / 10 M	
RKMV 4-07/...M	4	PVC	2 M / 5 M / 10 M	
RKMV 4-225/...M		PUR, halogen-free	2 M / 5 M / 10 M	
RKMV 8-354/...M	8	PUR, halogen-free	2 M / 5 M / 10 M	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumberg Automation:

[RKMWV 3-06/10 M](#) [RKMWV 3-06/3 M](#) [RKMWV 3-224/15 M](#) [RKMWV 3-224/3 M](#) [RKMWV 4-07/3 M](#) [RKMWV 4-225/3 M](#) [RKMWV 4-225/2 M](#) [RKMWV 4-225/5 M](#) [RKMWV 3-224/2 M](#) [RKMWV 3-224/5 M](#) [RKMWV 4-07/10 M](#) [RKMWV 4-07/2 M](#) [RKMWV 4-07/5 M](#) [RKMWV 4-225/10 M](#) [RKMV 8-354/10 M](#) [RKMV 8-354/2 M](#) [RKMWV 3-06/2 M](#) [RKMWV 3-06/5 M](#) [RKMWV 3-224/10 M](#) [RKMV 4-07/10 M](#) [RKMV 4-07/2 M](#) [RKMV 4-07/5 M](#) [RKMV 4-225/0,6 M](#) [RKMV 4-225/10 M](#) [RKMV 4-225/5 M](#) [RKMV 3-06/10 M](#) [RKMV 3-06/2 M](#) [RKMV 3-06/5 M](#) [RKMV 3-224/10 M](#) [RKMV 3-224/2 M](#) [RKMV 3-224/5 M](#) [RKMV 4-225/20 M](#) [RKMV 4-225/25 M](#) [RKMV 4-225/3 M](#) [RKMV 4-225/30 M](#) [RKMV 8-354/20 M](#) [RKMV 8-354/5 M](#) [RKMV 3-224/25M](#) [RKMV 3-224/3 M](#) [RKMV 3-224/30M](#) [RKMV 4-07/3 M](#) [RKMV 4-225/15 M](#) [RKMV 4-225/2 M](#) [RKMV 3-06/15 M](#) [RKMV 3-06/3 M](#) [RKMV 3-224/0,6 M](#) [RKMV 3-224/1 M](#) [RKMV 3-224/15 M](#) [RKMV 3-224/20 M](#)