

REZ200.NB3P



Article Number: 115-40200

Releasable Cable Tie, 7.9" Long, 30 lb Tensile Strength, PA66, Black, 100/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number REZ200.NB3P

Type REZ200

Color Black (BK)

Features and Benefits

- The unique, patented head design enables the tie to be inserted through a standard style head for permanent locking or can be twisted into the pinch-releasable style head for easy opening at a later time.
- The quick pinch-release mechanism can be released by one hand even when the tie is under tension.

Product Description HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Releasable Cable Tie, 7.9" Long, 30 lb Tensile Strength, PA66, Black, 100/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 30.0 lbs

Minimum Tensile Strength (Metric) 135 N

Length L (Imperial) 7.9 "

Length L (Metric) 200 mm

Fixation Method None

Identification Plate Position none

Releasable Closure Yes

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.19 "

Width W (Metric) 4.7 mm

Bundle Diameter Min. (Imperial) 0.63 "

Bundle Diameter Min. (Metric) 16.0 mm

Bundle Diameter Max. (Imperial) 2.0 "

Bundle Diameter Max. (Metric) 50.0 mm

Thickness T (Imperial) 0.055 "

Thickness T (Metric) 1.4 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 100 Pieces

Carton Quantity 6000 Pieces

Weight (Metric) 1.76 kg

Material and Specifications

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL94 V2

Operating Temperature -40°F to +185°F (-40°C to +85°C)

ROHS Compliant Yes