

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0009503031](#)
Status: **Active**
Overview: [KK Interconnect Systems](#)
Description: [KK 3.96mm Crimp Terminal Housing, Friction Ramp, 3 Circuits, Natural](#)

Documents:

Drawing (PDF)	Product Specification PS-08-50-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
3D Model	

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	2139
Application	Power, Wire-to-Board
Overview	KK Interconnect Systems
Product Name	KK 396
Taxonomy	Connector Housings
UPC	800753614017

Physical

Circuits (maximum)	3
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.784/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Temperature Range - Operating	See Product Specification

Solder Process Data


Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	2139-3A
--------------------	---------

Reference - Drawing Numbers

Product Specification	PS-08-50-001
Sales Drawing	SD-2139-001, SD-2139-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[2139](#) Series

Mates With

KK 396 Headers: [41771](#) , [41772](#) , [41791](#) ,
[41792](#) , [42491](#) , [42492](#) , KK 396 Breakaway
Headers: [41661](#) , [41662](#) , [41671](#) , [41672](#)

Use With

[2478](#) Crimp Terminals for 18-24 AWG, [2578](#)
Crimp Terminals for 22-26 AWG