

## TOLEDO BALL DIMMABLE

ToLEDo BALL V4 DIM FR 470LM 865 E14 SL

0026974



### Product features

- Compact and elegant design
- Suitable replacement for halogen, incandescent and compact fluorescent ball lamps
- Instant light at the flick of a switch
- Uniform light distribution
- Good colour rendering (CRI 80)
- Dimmable with approved dimmers
- Perfect for hotels, restaurants, lobbies, corridors, stairwells, reception areas
- Lower maintenance costs
- A+ energy rating



## PRODUCT OVERVIEW

Product name	ToLEDo BALL V4 DIM FR 470LM 865 E14 SL
Technology	LED
Watt (Rated) (W)	5.6
Type	TOLEDO BALL DIMMABLE
Cap/Base	E14
Fixture rating	Open
General application	Education, Hospitality, Residential & Consumer
ETIM Class	EC001959
E-number FI	4740511
Warranty	3 years
Luminous flux (lm)	470
Colour temperature (K)	6500
Light colour	Daylight
CRI (Ra)	80
Beam Angle (°)	160
Wattage (W)	5.6
Product Voltage (V)	230
Dimmable	Yes
Average life (Nominal) (h)	15000
Product EAN number	5410288269740

## DATA TABLE

### General data

Product name	ToLEDo BALL V4 DIM FR 470LM 865 E14 SL
Technology	LED
Watt (Rated) (W)	5.6
Type	TOLEDO BALL DIMMABLE
Cap/Base	E14
Fixture rating	Open
General application	Education, Hospitality, Residential & Consumer
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001959
E-number FI	4740511

## TOLEDO BALL DIMMABLE

*ToLEDo BALL V4 DIM FR 470LM 865 E14 SL*  
0026974

Warranty	3 years
----------	---------

### Optical data

Luminous flux (lm)	470
Luminous flux (Rated) (lm)	470
Colour temperature (K)	6500
Light colour	Daylight
CRI (Ra)	80
Beam Angle (°)	160

### Electrical data

Wattage (W)	5.6
Starting time (max) (s)	<0.5
Warm-up time to 60% of full light (max) (s)	<1.0
Mains voltage (V)	220-240V
Product Voltage (V)	230
Lamp power factor	0.5
No. Of switching cycles before premature failures	>50000
Dimmable	Yes
kWh per 1000 hours burning time	6
Nominal Frequency (Hz)	50/60Hz

### Lifetime data

Average life (Nominal) (h)	15000
Average life (Rated) (h)	15000

### Physical data

Nominal Product Length (mm)	81
Nominal Product Diameter (mm)	45
Weight (kg)	0.043

### Packaging

Single packaging type	Carton
Product EAN number	5410288269740
Packaging single length / height (cm)	9.6
Packaging single width (cm)	4.8
Packaging single depth (cm)	4.8
Units per inner package	6
Packaging inner length / height (cm)	15.51
Packaging inner width (cm)	10.5
Packaging inner depth (cm)	10.6
DUN14 (outer)	15410288269747
Units per outer package	60
Packaging outer length / height (cm)	55.0
Packaging outer width (cm)	32.6
Packaging outer depth (cm)	12.5

## TOLEDO BALL DIMMABLE

*ToLEDo BALL V4 DIM FR 470LM 865 E14 SL*

0026974

### Safety data

<b>Breakage cleaning instructions</b>	Not applicable
<b>Special purpose lamp</b>	No
<b>Dry applications use only</b>	Yes
<b>Suitable for household illumination</b>	Yes
<b>Safety message</b>	Not Suitable for totally enclosed fixtures

### TECHNICAL DRAWINGS

