

T-slot bolts



Application:

For clamping workpieces on machine tables.

Execution:

- Tempered
- Rolled thread
- Forged
- With milled groove guide
- M8 to M12, strength class 10.9
- M16 to M24, strength class 8.8
- DIN 787



Art. no.	26200 950
Brand	AMF
Manufacturer Part Number	85878
DIN	787
Thread dimension	M24
Groove width	24 mm
Length excluding head	200 mm
Outer diameter	23.7 mm
Thread length	125 mm
Length of head	40 mm
Head height	16 mm
Gross Weight	1.120 kg
Product Group	260

EAN

4020772085872