

Electronic micrometer

Digimatic

Mitutoyo

Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

Execution:

- carbide-tipped measuring faces
- IP65
- ABS function
- HOLD (measured value storage)
- Origin (measurement pre-setting up to 100 mm)
- Friction coupling for consistent, repeatable measuring force

Advantage:

- Long battery life, approx. 2.4 years
- IP65

Delivery:

Includes box, wrench, battery, setting standard (from 25 mm), up to 50-mm measuring range with factory test certificate



Art. no.	32017 345
Brand	MITUTOYO
Manufacturer Part Number	293-342-30
Display	Digital
Min./max. length measuring range in inches	2-3 in
Digit increment	0.001 mm
Measuring surface diameter	6.35 mm
IP protection class	IP 65
Spindle clamping	Yes
Digit height	7.5 mm
Functions	ABS function, Hold-function (AE lock), Origin (Dimension preset), Preset function, Automatic switch-off
Min./max. measurement force	5-10 N
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
DIN	863
Bracket depth	47 mm
Measuring spindle increments	0.635 mm
Calibration Group	D
Gross Weight	0.870 kg
Product Group	3MA

EAN

4946368673073