

## Pneumatic ratchet screwdriver 9022-2

Tightening torque 70 Nm



### Application:

For heavy screw-driving work in poorly accessible places.

### Advantage:

- Reduced vibration for effortless work

### Delivery:

Includes coupling plug



<b>Art. no.</b>	<b>75053 420</b>
<b>Brand</b>	HAZET
<b>Manufacturer Part Number</b>	9022-2
<b>Model</b>	9022-2
<b>Max. tightening torque</b>	70 Nm
<b>Max. idle speed</b>	160 rpm
<b>Air consumption</b>	180 l/min
<b>Tool holding device</b>	1/2-inch external square
<b>Connection thread</b>	G 1/4 inch
<b>Inner hose diameter</b>	10 mm
<b>Sound-pressure level</b>	88
<b>Valve design</b>	Lever valve
<b>Head height</b>	62 mm
<b>Length</b>	270 mm
<b>Weight</b>	1.2 kg
<b>With right/left-hand rotation</b>	Yes
<b>Gross Weight</b>	1.400 kg
<b>Product Group</b>	738

### EAN

4000896109456