

9012 EL-SPC pneumatic impact screwdriver



Application:

For heavy-duty screw-driving tasks.

Execution:

- 3 power levels in clockwise rotation, 1 power level in anti-clockwise rotation
- Exhaust air discharged downwards through the handle
- Thermally insulated handle

Advantage:

- One-handed operation thanks to innovative switching on the back of the device

Delivery:

Includes coupling plug



Art. no.	75065 031
Brand	HAZET
Manufacturer Part Number	9012EL-SPC
Model	9012 EL-SPC
Suitable for screw	M16
Max. tightening torque	1054 Nm
Max. releasing torque	1700 Nm
Max. idle speed	8000 rpm
Air consumption	139 l/min
Tool holding device	1/2-inch external square
Hammer mechanism system	Twin hammer mechanism
Length	185 mm
Connection thread	G 1/4 inch
Inner hose diameter	10 mm
Operating pressure	6.3 bar
Sound-pressure level	98.0
Weight	1.98 kg
With right/left-hand rotation	Yes
Gross Weight	2.320 kg
Product Group	738

EAN

4000896188444