



**Notes:**

1. Material and Finish:
  - Metal Cover: Brass, Nickel Plated
  - Ball Chain: Copper Alloy, Nickel Plated
  - ⓑ - Screw: Copper Alloy, Nickel Plated
  - ⓒ - Cover Gasket: Silicon, Color: White
2. Operating Temperature: -40°C to +85°C

Directive 2002/95/EC RoHS Compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY MANNER WITHOUT THE WRITTEN PERMISSION OF CONEC CORPORATION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION.	Customer:			Tolerance Unless otherwise specified 0 PLC ±0.50 1 PLC ±0.38 2 PLC ±0.25 3 PLC ±0.10 ANGLES ±3°		Scale: 1.5:1	Dim. in mm
	Name	Title	Approval Date			Material: See Notes	
						Title: Protective Cover Assembly Kit Metal Version Industrial Ethernet Connector (IP67)	
	d	1 x d	Jan/24/2014			Vincent Ke	Norm
c	1 x c	Apr/01/2010	Vincent ke	D-old			
b	1 x b	Jun/01/2009	Vincent Ke				
a	original						
Rev.	Changes	Date	Name	<b>CONEC®</b>		Drawing No.: 17K1A111	DIN A3
						Part No.: 17-100950	Sheet 1/1