

Han A Protect Cover Metal for Hood & Bas



Part number	09 20 032 5401
Specification	Han A Protect Cover Metal for Hood & Bas
HARTING eCatalogue	https://b2b.harting.com/09200325401

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A®
Type of hood/housing	Protection cover
Description of hood/housing	for hoods Metal
Type	Low construction High construction

Version

Locking type	Double locking lever
Size	32 A
Field of application	Standard Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Surface (hood/housing)	Powder-coated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Pushing Performance

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	28.08 g
Country of origin	Germany
Customs tariff number	85389099