HUBER+SUHNER[®] DATA SHEET Between Series Adapter: 31_BNC-N-50-1/133_U



Description

Adaptor jack/jack BNC jack (female) / N jack (female)

Interface standards IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

Mechanical Data

Number of matings Weight 500 0.0301 kg

Environmental Data

Operating Temperature 2002/95/EC (RoHS)

-65 °C to 165 °C compliant

Material Data

Piece Parts (BNC) Centre contact Outer contact Body Insulator

Piece Parts (N) Centre contact Outer contact Body Insulator

Related Documents

Catalogue drawing

Ordering Information

Single package

Material Copper Beryllium Alloy Brass Brass PFA / PTFE Material

Copper Beryllium Alloy Brass Brass PFA / PTFE

DCA-00014628

31 BNC-N-50-1/133 UE

Surface Plating

Gold Plating SUCOPLATE (R) Plating SUCOPLATE (R) Plating

Surface Plating

Gold Plating SUCOPLATE (R) Plating SUCOPLATE (R) Plating

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.

HUBER+SUHNER – Excellence in Connectivity Solutions

Document: DOC-0000195598 G.00



Uncontrolled Copy

 HUBER+SUHNER AG

 RF Technology

 9100 Herisau, Switzerland

 Phone
 +41 (0)71 353 41 11

 Fax
 +41 (0)71 353 45 90

 www.hubersuhner.com