



TREE 4TX METAL - UNMANAGED SWITCH - 4 PORTS

4 port unmanaged switch
(UL-Listed)

For connection cables please see chapter "Connection Technology"

[Link to Product](#)**Illustration**

Product may differ from Image

Approvals



Connections

Fieldbus	4 × RJ45
Supply System	Spring clamp plug-in terminal: 0.2...2.5 mm ²

Technical Data

Operating voltage	2 × 9...48 V DC, redundancy
Transfer rate	10/100 Mbit/s full duplex
Operating modes	Autocrossing Autonegotiation

General data

Protection	IP50
Housing	Metal black
Mounting method	DIN-rail mountable TH35 (EN 60715)
Temperature range	-10...+70 °C (storage temperature -40...+85 °C)
Dimensions H × W × D	110×22.5×89.6 mm

Diagnostic

Communication status	via LED
Monitoring - no voltage	yes

Commercial data

country of origin	TW
customs tariff number	85176200
minimum order quantity	1