

## Electronic micrometer

With large measuring range and interchangeable anvil

Mitutoyo

### Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

### Execution:

- carbide-tipped measuring faces
- IP65
- HOLD (measured value storage)
- Friction coupling for consistent, repeatable measuring force
- ABS function

### Advantage:

- Extra wide measuring range
- Interchangeable measuring anvil for a variable measuring range
- IP65
- Long battery life, approx. 2.4 years

### Delivery:

Includes box, setting standard, gauge slides, adjustment wrench, battery



<b>Art. no.</b>	<b>32017 384</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	340-524
<b>Display</b>	Digital
<b>Min./max. length measuring range</b>	700-800 mm
<b>Digit increment</b>	0.001 mm
<b>Measuring surface diameter</b>	6.3 mm
<b>Measuring arrangement</b>	Standard
<b>IP protection class</b>	IP 40
<b>Data transmission type</b>	DIGIMATIC
<b>Spindle clamping</b>	Yes
<b>Functions</b>	ABS function, Hold-function (AE lock), Preset function, Automatic switch-off
<b>Min./max. measurement force</b>	10-14 N
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Battery designation</b>	1,5 V SR44
<b>DIN</b>	863
<b>Measuring spindle increments</b>	0.5 mm
<b>Calibration Group</b>	D
<b>Gross Weight</b>	14.000 kg
<b>Product Group</b>	3MA

### EAN

4946368610511