

Verbindungsbrücken

□ 0,63mm – 2mm, isoliert

Connecting bridges


□ 0,63mm – 2mm, insulated

Douilles de liaisons

□ 0,63mm – 2mm, isolées

Typ Type Type	Bestell-Nr. Order No. No. de Cde	Isolation Griffteil Insulation handle Isolation	Temperaturbereich Operating temperature Température	Metalle / Oberfläche Metal parts / plating Partie métallique / traitement	Bemessungsstrom Rated current Intensité assignée	Steckweite Plug spacing Entraxe
			°C		A	mm

1:1




KB0,63-2,54/1	24.0058-*	PA	-40...80	Cu(Leg) ¹⁾ Cu(alloy) ¹⁾ Cu(alliage) ¹⁾	8	2,54
----------------------	------------------	----	----------	---	---	------

* Farben / Colours / Couleurs

22 23 24 28

1:1




KB1-2,54	24.0052-*	PA	-40...80	Cu(Leg) ¹⁾ Cu(alloy) ¹⁾ Cu(alliage) ¹⁾	10	2,54
-----------------	------------------	----	----------	---	----	------

* Farben / Colours / Couleurs

22 23 24 28

1:1



KB1-5,08	24.0050-*	PA	-40...80	Cu(Leg) ¹⁾ Cu(alloy) ¹⁾ Cu(alliage) ¹⁾	10	5,08
-----------------	------------------	----	----------	---	----	------

* Farben / Colours / Couleurs

22 23 24 28


¹⁾ Hartkupferlegierung, vergoldet

¹⁾ Hard-drawn copper alloy, gold plated

¹⁾ Alliage de cuivre dur, doré