




## USB A type, 2.0 Female Connector modular

Item No. 2001C199



mm±0.2



PIN NUMBER	SIGNAL NAME
1	VBUS
2	D-
3	D+
4	GND



Material:  
Housing: PP  
Insulator: LCP  
Connector shell: SPCC with plated Ni 40µ min.  
Contact: Brass with plated Au1µ

Technical:  
Voltage rating: 5V max.  
Current rating: 2A max.  
Contact resistance: 30mΩ max.  
Insulation resistance: 1000MΩ min.  
Dielectric withstanding voltage: 500V/AC(R.M.S)  
Operation temperature: -20 ~85°C