


V.345F Straight die grinder - 6 mm collet



Description:

- High speed 20000 RPM motor for efficient working.
- Built in air regulator which can be adjusted with a screwdriver.
- Feather teasing trigger for optimum control.
- Compact and lightweight tool designed for easy manoeuvrability.
- 6 mm collet for easy placing of grinding wheels, stones and other attachments.
- Free speed 20000 tr/min.
- Power 0,3 cv.
- Collet capacity 6 mm.
- Working pressure 6,2 bar.
- Average air consumption 113 l/min.
- Air inlet 1/4".
- Minimum hose diameter 10 mm - 3/8".
- Vibration <math><2,50\text{ m/s}^2\text{/a}</math>.
- Vibration 1,50 m/s²/K.
- Sound pressure 93,37 dB(A).
- Sound power 104,36 dB(A).

H [mm]: 62

L [mm]: 142

L1 [mm]: 40

[g]: 560
