

PROTECTIVE COVER FOR OP 177B AMOUNT: SEE TECHNICAL DATA



Product type designation	
Installation type/mounting	
Mounting in portrait format possible	Yes
Mounting in landscape format possible	Yes
Degree and class of protection	
IP (at the front)	IP65
Standards, approvals, certificates	
CE mark	Yes
Ambient conditions	
Ambient temperature in operation	
• Min.	0 °C
• max.	50 °C
Storage/transport temperature	
• Min.	-20 °C
• max.	60 °C
Relative humidity	
• Operation, max.	95 %
Mechanics/material	
Material of housing	
• plastic	Yes
Dimensions	
Width	274.3 mm

Height	243.26 mm
Thickness	7.8 mm
Mounting cutout, width	229 mm
Mounting cutout, height	196 mm

Weights

Without packaging	750 g
-------------------	-------

Scope of supply

Number of sets	2; 2 cover frames, 2 base frames, 2 protective covers
----------------	---

other

Note:	For OP177B
-------	------------

Usable in the following products

- Product 1 [6AV6642-0DC01-1AX0](#)
- Product 2 [6AV6642-0DA01-1AX0](#)
- Product 3 [6AV6642-0DC01-1AX1](#)
- Product 4 [6AV6642-0DA01-1AX1](#)

last modified: 12.03.2015