



Datenblatt - Fiche technique - Data sheet


21.15.8707



ROLINE LWL-Kabel 50/125 μ m OM3, LC/LC, türkis, 20m

ROLINE Câble FO 50/125 μ m, LC/LC, OM3, turquoise, 20m

ROLINE Fibre Optic Jumper Cable, 50/125 μ m, LC/LC, OM3, turquoise, 20m



21.15.8706	15m	turquoise
21.15.8707	20m	turquoise

Specification:

1. Connector Type : LC Multimode. (easy removable clip and Short Boat)
2. Cable Type :
 - 2-1 Zipcord Cable, $\varnothing 2.0\text{mm}$, OM3 50/125um Multimode. (300M/10G Fiber)
 - 2-2 Cable Jacket : Aqua color (Turq. color, 630C) PVC Material
3. Shrink Tube
4. Length : 15m and 20m

Performance:

- a. Insertion Loss : < 0.5 dB
- b. Fiber Extention : $-0.05\mu\text{m} < H < +0.05\mu\text{m}$
- c. $\varnothing 1.25\text{mm}$ Ferrule End-face Radius : $7 < R < 25\text{mm}$
- d. Apex Offset : $< 50\mu\text{m}$
- e. Increase in insertion loss after 500 mating : 0.2 dB Max
- f. Operating Temperature : -20° to $+70^{\circ}$
- g. Storage Temperature : -40° to $+80^{\circ}$

#: Matching DIM. ***: Important DIM. Others General DIM.	DRAWING	08.AUG.2013	
	CHECK	08.AUG.2013	
	APPROVAL	08.AUG.2013	
GENERAL TOLERANCE OF DIMENSIONS	ITEM NO. 21.15.8706, 21.15.8707		
X.XXX ±0.005 K.XX ±0.05 X.X ±0.1	SCALE	1/1 (A4)	DESC. ROLINE Fiber Optic Cable, OM3, LC/LC, 50/125um, Turq.
		UNIT	mm
		DRAWING CLASSIFICATION	S SHEET 1 OF 1

No.	MODIFIED AREA	ORIGINAL	MODIFY	DATE	MODIFIER
1					