

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1727040010](#)
Status: **Active**
Description: HPD Standard-Density D-Sub Receptacle Housing, Crimp, Panel Mount, 9 Circuits

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

General

Product Family	D-Sub Products
Series	172704
Exclude SD Check	Yes
IP Rating	IP20
Product Category	Receptacle
Product Literature Order No	987651-8284
Product Name	HPD
Type	Standard Density
UPC	889056019118

Physical


Circuits (Loaded)	0
Circuits (maximum)	9
Color - Resin	Black
Durability (mating cycles max)	500
Gender	Female
Lock to Mating Part	No
Material - Frame	Tin-plated Steel
Material - Resin	Thermoplastic
Net Weight	0.005/g
Number of Rows	2
Packaging Type	Carton
Panel Mount	Yes
Panel Mount Method	Flange
Polarized to Mating Part	Yes
Ports	1
Shielded	Yes
Temperature Range - Operating	-55° to +130°C
Waterproof / Dustproof	No
Waterproof / Dustproof Type	IP20

Electrical

Current - Maximum per Contact	7.5A
-------------------------------	------

Material Info

Engineering Number	FL09S7-K121
--------------------	-------------



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[172704](#) Series

Mates With

D-sub, Size 1, 9 position, Plug

Use With

HPD Standard-Density Female Crimp
Contacts [173112-0214](#) , [173112-0215](#) ,
[173112-0216](#)