

Products

B1 series | Single-pole switch 16A quick connection 6.3 black body



sample image

PRODUCT CODE: B111C11210000

Wiring diagrams



Terminal type



accessories

Body colour



Actuator colour



Marking



Marking colour



Rating


16 (6) A / 250 VAC
10 (4) A / 250 VAC - 5E4
T120/55 °C

20 A / 125 VAC
1/3 HP - 125 VAC
16 A / 250 VAC
3/4 HP - 250VAC
T105 °C


Approvals



Dimensions (mm)



Cut out (mm)



Z	Y	X
0.7-1.25	30.0 ⁰ _{-0.1}	11.0 ^{-0.3} ₋₀
1.25-2.0	30.2 ⁰ _{-0.1}	11.0 ^{-0.3} ₋₀
2.0-3.0	30.6 ⁰ _{-0.2}	11.0 ^{-0.3} ₋₀
3.0-4.0	30.8 ⁰ _{-0.2}	11.0 ^{-0.3} ₋₀

Termination

