

## Precision pointer snap gauges

Marameter FS



### Application:

For precise testing of cylindrical parts directly on the machine tool.

### Execution:

- Carbide measuring faces
- Movable anvil spring-mounted on bottom
- Consistent, repeatable measuring force
- Forged steel bracket
- Both measuring probes made from stainless, hardened steel
- Adjustable centring stop

### Delivery:

In wooden box, display unit not included



<b>Art. no.</b>	<b>31938 030</b>
<b>Brand</b>	MAHR
<b>Manufacturer Part Number</b>	4455001
<b>Min./max. length measuring range</b>	30-60 mm
<b>Measuring surface diameter</b>	17 mm
<b>Measurement force</b>	13.5 N
<b>Shank diameter</b>	8 mm
<b>Spindle clamping</b>	Yes
<b>Gross Weight</b>	1.972 kg
<b>Product Group</b>	305

### EAN

4059192017828

