

Precision pointer snap gauges

Marameter FS



Application:

For precise testing of cylindrical parts directly on the machine tool.

Version:

- Carbide measuring faces
- Movable anvil spring-mounted on bottom
- Consistent, repeatable measuring force
- Forged steel bracket
- Both measuring probes made from stainless, hardened steel
- Adjustable centring stop

Delivery:

In wooden box, display unit not included



Art. no.	31938 030
Min./max. length measuring range	30-60 mm
Measuring surface diameter	17 mm
Measurement force	13.5 N
Shaft diameter	8 mm
Spindle clamping	Yes

EAN-Code

4059192017828