

LED cordless work lamp

With spotlight, model MAG PRO



Execution:

- Light source COB LED light/spotlight: 1 x high-performance LED
- Luminous flux 90–900 lux/spotlight 2000 lux
- Luminous flux can be adjusted from 60–600 lumen (main lamp)
- Spotlight 150 lumen
- Power supply 3.7 V/2600 mAh Li-on
- IP 54 degree of protection

Advantage:

- Operating time 15 hours, charging time 4 hours

Delivery:

USB cable 1 m, operating instructions



Art. no.	56831 012
Brand	SCANGRIP
Manufacturer Part Number	03.5690
Model	MAG PRO
Length	261 mm
Luminous flux	600 lm
Nominal voltage	3.7 V/DC
IP protection class	IP 54
Gross Weight	0.400 kg
Product Group	51C

EAN

5708997356906