



Unsere Ideen bewegen Menschen ...
Our inventions move people ...



Unsere Ideen bewegen Menschen ...
Our inventions move people ...

Räder Wheels

Büro für Gestaltung Thorsten Ellermann, Bielefeld



Germany
Rolko Kohlgrüber GmbH
Industriestraße 14
D-33829 Borgholzhausen

Phone +49 5425 9402-0
Fax +49 5425 9402-20

www.rolko.com
info@rolko.com

Danmark
Rolko Scandinavia ApS
Suensonvej 2
DK-8600 Silkeborg

Phone +45 87 20 18 88
Fax +45 86 81 86 88

www.rolko.com
RolkoDK@rolko.com

Poland
Rolko Polska s.p.z.o.o.
ul. Paderewskiego 3 b
PL-59400 Jawor

Phone +48 76 870 70 70
Fax +48 76 870 70 20

www.rolko.com
RolkoPL@rolko.com

Netherlands
Rolko Nederland bv
Limburghaven 2b
NL-3433 PK Nieuwegein

Phone +313 02 41 32 30
Fax +313 02 54 16 55

www.rolko.com
RolkoNL@rolko.com

**Räder | Wheels
2006**

ROLKO Räder von 3" bis 16" aus hochwertigem Kunststoff oder Aluminium sind speziell für die Rehabilitationsbranche entwickelt. Ob Vorderrad für Standard-, Sport-, Kinderrollstuhl, Buggy oder Rehagerät, wir fertigen für jeden Einsatzbereich das passende Rad. Eine Vielzahl von Reifen ermöglichen Varianten von komfortablen über sportlichen bis pannensicheren Einsatz.

Rolko wheels from 3" to 16" are manufactured from high quality plastic or aluminium and have been developed especially for the rehabilitation industry. Whether it be wheels for sports, children's wheelchair, buggy or rehabilitation equipment, ROLKO has the right wheel for every application. Using a wide variety of tyres allows us to feature on comfort, performance (sporting) and puncture protection!



Räder | Wheels 2006



*Unsere Ideen bewegen Menschen ...
Our inventions move people ...*

Räder Wheels

Inhalt | Content

Räder mit Vollgummireifen | Wheels with rubber tyre **4**

Räder mit Polyurethanreifen | Wheels with polyurethane tyre **8**

Räder mit EVA-Reifen | Wheels with EVA tyre **14**

Räder mit Luftbereifung | Wheels with pneumatic tyre **18**

Räder mit Rolkofill | Wheels with Rolkofill **26**



Aluminiumfelge | Aluminium rim

						Art.-Nr Art.-No
100	24	8	25	608	50	R100/24-VA

Reifen schwarz, spurlos | Tyre black, no marks

						Art.-Nr Art.-No
100	24	8	25	608	50	R100/24-VAS

Aluminiumfelge | Aluminium rim

						Art.-Nr Art.-No
125	24	8	25	608	50	R125/24-VA

Reifen schwarz, spurlos | Tyre black, no marks

						Art.-Nr Art.-No
125	24	8	25	608	50	R125/24-VAS

Aluminiumfelge, 2-teilig | Aluminium rim, 2-parted

						Art.-Nr Art.-No
100	24	8	25	608	50	R100/24-2-VA

Reifen schwarz, spurlos | Tyre black, no marks

						Art.-Nr Art.-No
100	24	8	25	608	50	R100/24-2-VAS

ROLKO-Vollgummireifen ohne schwarze Abriebspuren

| ROLKO-rubber tyres without black skid-marks



Kunststofffelge | Plastic rim

						Art.-Nr Art.-No
100	24	8	25	608	50	R100/24-5-V

Reifen schwarz, spurlos | Tyre black, no marks

						Art.-Nr Art.-No
100	24	8	25	608	50	R100/24-5-VS

Kunststofffelge | Plastic rim

						Art.-Nr Art.-No
125	24	8	25	608	50	R125/24-5-V

Reifen schwarz, spurlos | Tyre black, no marks

						Art.-Nr Art.-No
125	24	8	25	608	50	R125/24-5-VS

Kunststofffelge | Plastic rim

						Art.-Nr Art.-No
100	32	8	33	608	50	R100/32-2-V-2RS

Reifen schwarz, spurlos | Tyre black, no marks

						Art.-Nr Art.-No
100	32	8	33	608	50	R100/32-2-VS-2RS

Kunststofffelge | Plastic rim

						Art.-Nr Art.-No
125	32	8	33	608	50	R125/32-2-V-2RS



Kunststofffelge | Plastic rim

							Art-Nr Art-No
125	25	8	36	6000	50	R125/25-2-V-S	
125	25	8	46	6000	50	R125/25-2-V-S46	



2-Komponentenreifen/ | 2-component tyre

							Art-Nr Art-No
125	25	8	36	6000	50	R125/25-2-V-S2K	
125	25	8	46	6000	50	R125/25-2-V-S2K46	

Kunststofffelge | Plastic rim

							Art-Nr Art-No
150	25	8	36	6000	50	R150/25-2-V-S	
150	25	8	46	6000	50	R150/25-2-V-S46	

2-Komponentenreifen/ | 2-component tyre

							Art-Nr Art-No
150	25	8	36	6000	50	R150/25-2-V-S2K	
150	25	8	46	6000	50	R150/25-2-V-S2K46	

Kunststofffelge | Plastic rim

							Art-Nr Art-No
150	33	8	36	6000	50	R150/33-2-V-8/36	
150	33	8	46	6000	50	R150/33-2-V-8/46	
150	33	8	60	6000	50	R150/33-2-V-8/60	
150	33	8	36	608	50	R150/33-2-V-S608RS	

Kunststofffelge | Plastic rim

							Art-Nr Art-No
150	34	8	36	6000	50	R150/34-2-V-S2K	
150	34	8	46	6000	50	R150/34-2-V-S2K-46	



Kunststofffelge | Plastic rim

							Art-Nr Art-No
125	37,5	8	43	6000	60	R125/37,5-VLI-P	
125	37,5	8	43	608	60	R125/37,5-VLI6RS	



Kunststofffelge | Plastic rim

							Art-Nr Art-No
140	40	8	58	6000	60	R140/40-1-V	
140	40	8	46	6000	60	R140/40-1-V-46	



Kunststoff Hohlspicenfelge | Plastic rim hollow spokes

							Art-Nr Art-No
178	35	8	60	SK	50	R178/35-3-V	
178	35	8	46	6000	50	R178/35-3-V-46	



Kunststofffelge | Plastic rim

							Art-Nr Art-No
178	30	8	60	SK	60	R178/30-1-V-S	
178	30	8	46	6201	60	R178/30-1-V-S46	
200	25	8	46	6201	75	R200/25-1-V-S46	
200	25	8	60	SK	75	R200/25-1-V-SSK	



2-Komponentenreifen/ | 2-component tyre

							Art-Nr Art-No
178	30	8	60	SK	50	R178/30-1-V-S2K	
178	30	8	46	6201	50	R178/30-1-V-S2K46	





Kunststofffelge, 2-teilig. | Plastic rim, 2-parted

							Art.-Nr Art.-No
173	43	8	60	SK	50		R180/45-2-PU-S
200	50	8	60	SK	50		R200/50-2-PU-S



Kunststofffelge | Plastic rim

							Art.-Nr Art.-No
173	43	8	60	-	SK	50	R180/45-1-PUSK
173	43	12	-	46	6201	50	R180/45-1-PUS12
200	50	8	60	-	SK	50	R200/50-1-PUSK
200	50	12	-	46	6201	50	R200/50-1-PUS12-K



Kunststofffelge | Plastic rim

							Art.-Nr Art.-No
173	43	8	60	SK	50		R180/45-3-PU-SK
173	43	8	45	6000	50		R180/45-3-PUS45
200	50	8	60	SK	50		R200/50-3-PU-SK



Rollatorrad | Rollator wheel

							Art.-Nr Art.-No
200	50	8	62	608		40	R200/50-TPE

Kunststoff Hohlspeichenfelge | Plastic rim hollow spokes

							Art.-Nr Art.-No
173	43	8	60	SK	50		R180/45-H3-PU-SK
173	43	8	46	6000	50		R180/45-H3-PU46
200	50	8	60	SK	50		R200/50-H3-PU-SK



Kunststoff Hohlspeichenfelge | Plastic rim hollow spokes

							Art.-Nr Art.-No
300	45	12	54	-	6201	50	R300/45-5-PUS
300	45	12	-	47	6201	50	R300/45-5-PUS-K



Kunststoff Hohlspeichenfelge | Plastic rim hollow spokes

					Schraube/ Bolt			Art.-Nr Art.-No
300	45	12	43	M12x100	6001/6201	50		R300/45-5-PUSBL
300	45	12	43	M12x100	6001/6201	50		R300/45-5-PUSBR

BL = Bremse links | Brake left

BR = Bremse rechts | Brake right



Kunststofffelge | Plastic rim

							Art.-Nr Art.-No
300	40	12	54	-	6201	50	R300/40-3-PUS
300	40	12	-	47	6201	50	R300/40-3-PUS-K





Kunststofffelge | Plastic rim

Art-Nr Art-No	
250	50 12 54 - 6201 50 R250/50-2-PU-S
250	50 12 - 47 6201 50 R250/50-2-PUS-K
300	45 12 54 - 6201 50 R300/45-2-PU-S
300	45 12 - 47 6201 50 R300/45-2-PUS-K



Kunststofffelge | Plastic rim

Art-Nr Art-No	
300	46 12 43 M12x100 6001/6201 50 R300/45-2-PUSBL
300	46 12 43 M12x100 6001/6201 50 R300/45-2-PUSBR

BL = Bremse links | Brake left

BR = Bremse rechts | Brake right



Kunststofffelge | Plastic rim

Art-Nr Art-No	
250	50 12 54 - 6201 50 R250/50-1-PU-S
250	50 12 - 47 6201 50 R250/50-1-PUS-K
300	45 12 54 - 6201 50 R300/45-1-PU-S
300	45 12 - 47 6201 50 R300/45-1-PUS-K



Kunststofffelge | Plastic rim

Art-Nr Art-No	
250	50 12 43 M12x100 6001/6201 50 R250/50-1-PUSBL
250	50 12 43 M12x100 6001/6201 50 R250/50-1-PUSBR
300	45 12 43 M12x100 6001/6201 50 R300/45-1-PUSBL
300	45 12 43 M12x100 6001/6201 50 R300/45-1-PUSBR

BL = Bremse links | Brake left

BR = Bremse rechts | Brake right

Kunststofffelge | Plastic rim

Art-Nr Art-No	
320	63 12 54 - 6201 75 R320/63-V-PUS
320	63 12 - 47 6201 75 R320/63-V-PUS-K



Kunststofffelge | Plastic rim

Art-Nr Art-No	
320	63 12 44 M12x100 6001/6201 75 R320/63-V-PUSBL
320	63 12 44 M12x100 6001/6201 75 R320/63-V-PUSBR

BL = Bremse links | Brake left

BR = Bremse rechts | Brake right



Kunststofffelge | Plastic rim

Art-Nr Art-No	
370	35 12 47 6201 60 R370/35-1-PUG-K
400	40 12 47 6201 60 R400/40-1-PUG-K
415	60 12 47 6201 60 R415/60-1-PUG-K



Kunststofffelge | Plastic rim

Art-Nr Art-No	
370	35 12 44 M12x100 6001/6201 60 R370/35-1-PUGBL
370	35 12 44 M12x100 6001/6201 60 R370/35-1-PUGBR
400	40 12 44 M12x100 6001/6201 60 R400/40-1-PUGBL
400	40 12 44 M12x100 6001/6201 60 R400/40-1-PUGBR
415	60 12 44 M12x100 6001/6201 60 R415/60-1-PUGBL
415	60 12 44 M12x100 6001/6201 60 R415/60-1-PUGBR

BL = Bremse links | Brake left

BR = Bremse rechts | Brake right





Kunststofffelge | Plastic rim

							Art.-Nr Art.-No
150	30	8	36	6000	40	R150/30-1-ES	



Kunststofffelge | Plastic rim

							Art.-Nr Art.-No
150	30	8	36	6000	40	R150/30-1-ES-R	



Kunststofffelge | Plastic rim

							Art.-Nr Art.-No
200	50	8	60	SK	40	R200/50-1-ES-R	



Kunststofffelge | Plastic rim

							Art.-Nr Art.-No
200	50	8	60	SK	40	R200/50-3-EBS-SK	

Kunststofffelge | Plastic rim

							Art.-Nr Art.-No
150	30	8	36	-	6000	40	R150/30-1-ESSRR
150	30	10	-	21	6000	40	R150/30-1-ESSRR10-K



Kunststofffelge | Plastic rim

							Art.-Nr Art.-No
200	30	12	36	6001	40	R200/30-1-ESSRR-K	



Kunststofffelge | Plastic rim

							Art.-Nr Art.-No
180	45	8	60	SK	40	R180/45-1-ESSRAC-SK	



Kunststofffelge | Plastic rim

							Art.-Nr Art.-No
250	50	12	47	6201	40	R250/50-1-ESSRAC-K	





Kunststofffelge | Plastic rim

							Art.-Nr Art.-No
200	30	12	59	GL	40	R200/30-2-ES-GL	



Kunststofffelge | Plastic rim

							Art.-Nr Art.-No
200	30	12	-	45	6201	40	R200/30-2-ES-PK
200	30	8	60	-	SK	40	R200/30-2-ES-SK



Kunststofffelge | Plastic rim

							Art.-Nr Art.-No
250	50	12	54	-	6201	40	R250/50-2-E-S
250	50	12	-	47	6201	40	R250/50-2-E-S-K



Kunststofffelge | Plastic rim

							Art.-Nr Art.-No
300	50	12	54	-	6201	40	R300/50-2-E-S
300	50	12	-	47	6201	40	R300/50-2-E-S-K

Kunststofffelge | Plastic rim

						Art.-Nr Art.-No
180	45	8	60	SK	40	R180/45-6-ESG-SK



Kunststofffelge | Plastic rim

						Art.-Nr Art.-No
250	50	12	47	6201	40	R250/50-6-ESG-K



Kunststofffelge | Plastic rim

						Art.-Nr Art.-No
250	50	12	54	6201	40	R250/50-6-ESG-Z-K



Zahnkranz für Radfeststeller | Gear ring for wheel lock

Kunststofffelge | Plastic rim

Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm	
150	30	8	36	6000	6x1.1/4"	60	R150/30-2-L-S	150	30	8	46	6000	6x1.1/4"	60	R150/30-2-L-S46								
150	30	8	36	6000	6x1.1/4"	60	R150/30-2-L-S	150	30	8	46	6000	6x1.1/4"	60	R150/30-2-L-S46								

Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm	
150	30	8	36	6000	6x1.1/4"	60	R150/30-2-L-SSL																
150	30	8	36	6000	6x1.1/4"	60	R150/30-2-L-SSL																

Kunststofffelge | Plastic rim

Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm	
150	30	8	36	6000	6x1.1/4"	60	R150/30-1-L-S	150	30	8	46	6000	6x1.1/4"	60	R150/30-1-L-S46								
150	30	8	36	6000	6x1.1/4"	60	R150/30-1-L-S	150	30	8	46	6000	6x1.1/4"	60	R150/30-1-L-S46								

Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm	
150	30	8	36	6000	6x1.1/4"	60	R150/30-1-L-SSL																
150	30	8	36	6000	6x1.1/4"	60	R150/30-1-L-SSL																

Kunststofffelge | Plastic rim

Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm	
200	30	8	38	608	8x1.1/4"	75	R200/30-1-L-S38	200	30	8	46	6001	8x1.1/4"	75	R200/30-1-L-S46	200	30	8	60	SK	8x1.1/4"	75	R200/30-1-L-S5K
200	30	8	38	608	8x1.1/4"	75	R200/30-1-L-S38	200	30	8	46	6001	8x1.1/4"	75	R200/30-1-L-S46	200	30	8	60	SK	8x1.1/4"	75	R200/30-1-L-S5K

Kunststofffelge | Plastic rim

Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm	
200	30	12	45	M12x100	6001/6201	8x1.1/4"	75	R200/30-1-LGSBL	200	30	12	45	M12x100	6001/6201	8x1.1/4"	75	R200/30-1-LGSBR						
200	30	12	45	M12x100	6001/6201	8x1.1/4"	75	R200/30-1-LGSBL	200	30	12	45	M12x100	6001/6201	8x1.1/4"	75	R200/30-1-LGSBR						

BL = Bremse links | Brake left
BR = Bremse rechts | Brake right

Kunststofffelge | Plastic rim

Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm	
180	45	8	46	6000	7x1.3/4"	75	R180/45-H3-LGS46	180	45	8	60	SK	7x1.3/4"	75	R180/45-H3-LGS5K	200	50	8	60	SK	8x2"	75	R200/50-H3-LGS5K
180	45	8	46	6000	7x1.3/4"	75	R180/45-H3-LGS46	180	45	8	60	SK	7x1.3/4"	75	R180/45-H3-LGS5K	200	50	8	60	SK	8x2"	75	R200/50-H3-LGS5K

Kunststofffelge | Plastic rim

Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm	
180	45	8	45	6000	7x1.3/4"	75	R180/45-3-LGS45	180	45	8	60	SK	7x1.3/4"	75	R180/45-3-LGS5K	200	50	8	60	SK	8x2"	75	R200/50-3-LGS5K
180	45	8	45	6000	7x1.3/4"	75	R180/45-3-LGS45	180	45	8	60	SK	7x1.3/4"	75	R180/45-3-LGS5K	200	50	8	60	SK	8x2"	75	R200/50-3-LGS5K

Kunststofffelge, 2-teilig | Plastic rim, 2-parted

Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm	
180	45	8	60	SK	7x1.3/4"	75	R180/45-2-LG-S	200	50	8	60	SK	8x2"	75	R200/50-2-LG-S								
180	45	8	60	SK	7x1.3/4"	75	R180/45-2-LG-S	200	50	8	60	SK	8x2"	75	R200/50-2-LG-S								

Kunststofffelge | Plastic rim

Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm	
180	45	8	60	SK	7x1.3/4"	75	R180/45-1-LGSAV	200	45	8	60	SK	8x2"	75	R200/50-1-LGSAV								
180	45	8	60	SK	7x1.3/4"	75	R180/45-1-LGSAV	200	45	8	60	SK	8x2"	75	R200/50-1-LGSAV								

Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm		Zoll		mm	
180	45	12	46	6201	7x1.3/4"	75	R180/45-1-LG12-K	200	50	12	46	6201	8x2"	75	R200/50-1-LG12-K								
180	45	12	46	6201	7x1.3/4"	75	R180/45-1-LG12-K	200	50	12	46	6201	8x2"	75	R200/50-1-LG12-K								



Kunststofffelge | Plastic rim

						Zoll Inch		Art.-Nr Art.-No
180	45	8	60	SK	7x1.3/4"	75	R180/45-6-LSG-IA-SK	



Kunststofffelge | Plastic rim

					Zoll Inch		Art.-Nr Art.-No
250	50	12	47	6201	10x2"	75	R250/50-6-LSG-IA-K



Kunststofffelge | Plastic rim

					Zoll Inch		Art.-Nr Art.-No
250	50	12	47	6201	10x2"	75	R250/50-6-LSG-IA-Z-K



Zahnkranz für Radfeststeller
| Gear ring for wheel lock

Kunststofffelge | Plastic rim

					Zoll Inch		Art.-Nr Art.-No
190	50	8	60	SK	75	R190/50-3-LS-SK	

					Zoll Inch		Art.-Nr Art.-No
190	50	8	60	SK	75	R190/50-3-LSSI-SK	



Kunststofffelge | Plastic rim

					Zoll Inch		Art.-Nr Art.-No
180	45	8	60	SK	7x1.3/4"	75	R180/45-1-LSRAC-SK



Kunststofffelge | Plastic rim

					Zoll Inch		Art.-Nr Art.-No
250	50	12	47	6201	10x2"	75	R250/50-1-LSRACS-K





Kunststofffelge | Plastic rim

Art-Nr Art-No	Zoll Inch	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No
200	30	12	-	45	6201	8x1.1/4"	40	R200/30-2-LG-K	
200	30	8	60	-	SK	8x1.1/4"	40	R200/30-2-LG-SK	



Kunststofffelge | Plastic rim

Art-Nr Art-No	Zoll Inch	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No
250	50	12	54	-	6201	10x2"	75	R250/50-2-LGS	
250	50	12	-	47	6201	10x2"	75	R250/50-2-LGS-K	



Kunststofffelge | Plastic rim

Art-Nr Art-No	Zoll Inch	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No
310	55	12	54	-	6201	12.1/2x2.1/4"	75	R310/55-2-LGS	
310	55	12	-	47	6201	12.1/2x2.1/4"	75	R310/55-2-LGS-K	



Kunststofffelge | Plastic rim

Art-Nr Art-No	Zoll Inch	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No
310	55	12	45	M12x100	6001/6201	12.1/2x2.1/4"	75	R310/55-2-LGSBL	
310	55	12	45	M12x100	6001/6201	12.1/2x2.1/4"	75	R310/55-2-LGSBR	

BL = Bremse links | Brake left
BR = Bremse rechts | Brake right

Kunststoff Hohlspeichenfelge | Plastic rim hollow spokes

Art-Nr Art-No	Zoll Inch	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No
310	55	12	54	-	6201	12.1/2x2.1/4"	75	R310/55-5-LGS	
310	55	12	-	47	6201	12.1/2x2.1/4"	75	R310/55-5-LGS-K	



Kunststoff Hohlspeichenfelge | Plastic rim hollow spokes

Art-Nr Art-No	Zoll Inch	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No
310	55	12	43	M12x100	6001/6201	12.1/2x2.1/4"	75	R310/55-5-LGSBL	
310	55	12	43	M12x100	6001/6201	12.1/2x2.1/4"	75	R310/55-5-LGSBR	



BL = Bremse links | Brake left
BR = Bremse rechts | Brake right

Kunststofffelge | Plastic rim

Art-Nr Art-No	Zoll Inch	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No
250	50	12	54	-	6201	10x2"	75	R250/50-1-LGS	
250	50	12	-	47	6201	10x2"	75	R250/50-1-LGS-K	
310	55	12	54	-	6201	12.1/2x2.1/4"	75	R310/55-1-LGS	
310	55	12	-	47	6201	12.1/2x2.1/4"	75	R310/55-1-LGS-K	



Kunststofffelge | Plastic rim

Art-Nr Art-No	Zoll Inch	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No	Art-Nr Art-No
250	50	12	43	M12x100	6001/6201	10x2"	75	R250/50-1-LGSBL	
250	50	12	43	M12x100	6001/6201	10x2"	75	R250/50-1-LGSBR	
310	55	12	43	M12x100	6001/6201	12.1/2x2.1/4"	75	R310/55-1-LGSBL	
310	55	12	43	M12x100	6001/6201	12.1/2x2.1/4"	75	R310/55-1-LGSBR	



BL = Bremse links | Brake left
BR = Bremse rechts | Brake right



Kunststofffelge | Plastic rim

Art.-Nr Art.-No	Zoll Inch	6201	54	12	55	310
R310/55-V-LGS	12.1/2x2.1/4"	6201	-	12	55	310
R310/55-V-LGS-K	12.1/2x2.1/4"	6201	47	12	55	310
R310/55-V-LGVS	12.1/2x2.1/4"	6201	-	12	60	330
R310/55-V-LGVS-K	12.1/2x2.1/4"	6201	47	12	60	330



Kunststofffelge | Plastic rim

Art.-Nr Art.-No	Zoll Inch	6001/6201	43	12	55	310
R310/55-V-LGSBL	12.1/2x2.1/4"	6001/6201	M12x100	12	55	310
R310/55-V-LGSBR	12.1/2x2.1/4"	6001/6201	M12x100	12	55	310
R310/55-V-LGVSBL	12.1/2x2.1/4"	6001/6201	M12x100	12	60	330
R310/55-V-LGVSBR	12.1/2x2.1/4"	6001/6201	M12x100	12	60	330

BL = Bremse links | Brake left

BR = Bremse rechts | Brake right



Kunststofffelge | Plastic rim

Art.-Nr Art.-No	Zoll Inch	6201	50	12	45	400
R400/45-1-LGS-K	16x1.75"	6201	50	12	45 <td>400</td>	400
R420/55-1-LGS-K	16x2.125"	6201	50	12	55 <td>420</td>	420



Kunststofffelge | Plastic rim

Art.-Nr Art.-No	Zoll Inch	6001/6201	44	12	45	400
R400/45-1-LGSBL	16x1.75"	6001/6201	M12x100	12	45 <td>400</td>	400
R400/45-1-LGSBR	16x1.75"	6001/6201	M12x100	12	45 <td>400</td>	400
R420/55-1-LGSBL	16x2.125"	6001/6201	M12x100	12	55 <td>420</td>	420
R420/55-1-LGSBR	16x2.125"	6001/6201	M12x100	12	55 <td>420</td>	420

BL = Bremse links | Brake left

BR = Bremse rechts | Brake right

ROLKO Räder können Ihren speziellen Anforderungen angepasst werden. Wir fertigen Naben, Achsen und Trommelbremsen nach Ihren Wünschen. Bereifungsmöglichkeiten finden Sie in der Rubrik 5 Bereifungen. Alle Ausführungen der Bremsanker sind in der Rubrik 6 Bremsen zusammengefasst.

ROLKO wheels can be supplied to customer specifications, including hubs, axles or drum brakes by using the tyres from section 5 and the brake components from section 6.



Schnellverschluß für 10 oder 12 mm Achsen
| Quick lock for 10 or 12 mm axle



Bereifung optional in Farbe schwarz
| Tyres optional in colour black



Weitere Felgenfarben auf Anfrage
| Further colours of rims on request



Bremse links | Brake left



Bremse rechts | Brake right



Nabenabdeckkappen optional
| Hub caps optional





Kunststoffelge | Plastic rim

Art-Nr Art.-No	Zoll Inch	60	6000	36	8	30	150
R150/30-2-F-S	6x1.1/4"	60	6000	36	8	30	150
R150/30-2-F-S46	6x1.1/4"	60	6000	46	8	30	150

Art-Nr Art.-No	Zoll Inch	60	6000	36	8	30	150
R150/30-1-F-S	6x1.1/4"	60	6000	36	8	30	150
R150/30-1-F-S46	6x1.1/4"	60	6000	46	8	30	150

Art-Nr Art.-No	Zoll Inch	60	SK	60	8	50	200
R200/50-3-FGSSK	8x2"	60	SK	60	8	50	200

Kunststoffelge, 2-teilig | Plastic rim, 2-parted

Art-Nr Art.-No	Zoll Inch	75	SK	60	8	45	180
R180/45-2-F-S	7x1.3/4"	75	SK	60	8	45	180
R200/50-2-F-S	8x2"	75	SK	60	8	50	200

Kunststoffelge | Plastic rim

Art-Nr Art.-No	Zoll Inch	60	6201	31	15	50	200
R200/50-1-FGG15-So	8x2"	60	6201	31	15	50	200



Kunststoffelge | Plastic rim

Art-Nr Art.-No	Zoll Inch	75	6201	47	12	50	250
R250/50-1-F-S	10x2"	75	6201	47	12	50	250
R310/55-1-F-S	12.1/2x2.1/4"	75	6201	47	12	55	310

Weitere Räder mit pannensicheren Rolkofill Reifen auf Anfrage

| Further wheels with Rolkofill tyre on request



Pannensichere Reifen mit hochwertigen ROLKOFILL-Einlagen für alle Größen

| Antipuncture tyres with high quality ROLKOFILL inserts for all sizes



Alle Maße sind ca.-Angaben.

Abbildungen unverbindlich. Änderungen vorbehalten.

Wir liefern gemäß unseren neuesten Verkaufs- und Lieferbedingungen.

All measures are approx. informations.

Illustrations are not binding. Changings possible.

We deliver as our latest general delivery conditions.