PHILIPS Lighting



MASTER TL-E Circular Super 80

TL-E 32W/865 1CT/12

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes, including decorative ones, in 'human' applications such as schools, offices, shops and homes, and for lighting of residential areas.

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		LLMF 2000 h Rated	84 %	
Cap-Base	G10Q [G10q]	LLMF 4000 h Rated	79 %	
ife to 50% Failures (Nom)	13000 h	LLMF 6000 h Rated	75 %	
LSF 2000 h Rated	98 %	LLMF 8000 h Rated	73 %	
LSF 4000 h Rated	77 %			
LSF 6000 h Rated	60 %	Operating and Electrical		
LSF 8000 h Rated	45 %	Power (Nom)	32.0 W	
		Lamp Current (Nom)	0.450 A	
Light Technical		Voltage (Nom)	81 V	
Color Code	865 [CCT of 6500K]			
Luminous Flux (Nom)	2310 lm	Temperature	Temperature	
Luminous Flux (Rated) (Nom)	2310 lm	Design Temperature (Nom)	25 °C	
Color Designation	Cool Daylight			
Correlated Color Temperature (Nom)	6500 K	Controls and Dimming	Controls and Dimming	
uminous Efficacy (rated) (Nom)	72 lm/W	Dimmable	Yes	
Color Rendering Index (Nom)	80			

MASTER TL-E Circular Super 80

Approval and Application			
Energy Efficiency Label (EEL)	А		
Mercury (Hg) Content (Nom)	8 mg		
Energy Consumption kWh/1000 h	35 kWh		
Product Data			
Full product code	872790084055100		
Order product name	TL-E 32W/865 1CT/12		
EAN/UPC - Product	8727900840551		

Order code	928026386570
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	928026386570
Net Weight (Piece)	0.180 kg
ILCOS Code	FSC-32/65/1B-E-G10q-29/299

Dimensional drawing



TL-E 32W/865

Product	D (max)	D (min)	E (min)	E (max)	I (min)	l (max)
TL-E 32W/865	30.9 mm	27.1 mm	299.0 mm	303.5 mm	241.0 mm	246.0 mm
1CT/12						



© 2020 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.