



Standard lamps

Dental technology


For special features, specific benefits and areas of use see page 104



Article no.	Description	V	W	Am- perage	Cap	Bulb diameter D mm	Total length max. mm	Light centre length mm	Luminous flux lm	Average life h	Individual life h	Burning position	PU
00936054	24V 1.4A P45t transversal	24		1.4		40	76	35	430	600			
00936055	24V 1.4A P45t transversal	24		1.4		40	76	28	430	600			
00936063	24V 1.6A P45t transversal	24		1.6		40	76	28	500	600			



Article no.	Description	V	W	Am- perage	Cap	Bulb diameter D max. mm	Total length L max. mm	Light centre length mm	Luminous flux lm	Average life h	Individual life h	Burning position	PU
00936062	24V 40W BA15d/24x17 50x76 kv	24	40		BA15d	50	76		550	500			



Article no.	Description	V	W	Am- perage	Cap	Bulb diameter max. mm	Total length max. mm	Light centre length mm	Lumi- nous flux lm	Average life h	Individual life h	Burning position	PU
8600127500	reflector lamp 12V 75W with heat shield	12	75		Special				2,300	300			