


Data Sheet

Metal Cable Gland – PG series



Material: Nickel-plated brass
 Claw: PA66 (Nylon), UL94-V2
 Hermetic seal: NBR, Silicone rubber
 O-Ring: NBR, Silicone rubber
 Protection degree: IP68-10 bar
 Temperature: Static state: -40 °C to 100 °C, Short time to 120 °C;
 Dynamic state: -20 °C to 80 °C, Short time to 100 °C

Unit: mm

Item no.	Item	Ø Cable range	GL Thread Length	AG Thread O.D.	Mounting hole	H Joint Length	Spanner size
2575717	PG7	3-6.5	6.5	12.5	12.5-12.7	17	14/15
2575718	PG9	4-8	8	15.2	15.2-15.4	19	17/18
2575719	PG11	5-10	8	18.6	18.6-18.8	21	20/21
2575720	PG13.5	6-12	8	20.4	20.4-20.6	22	22/23
2575721	PG16	10-14	8	22.5	22.5-22.7	23	24/25
2575722	PG21	13-18	9	28.3	28.3-28.5	27	30
2575723	PG29	18-25	10	37.0	37.0-37.2	31	40
2576349	PG36	25-33	11	47.0	47.0-47.2	37	50