

Signal lamps with integrated filament lamp - 5 mm



Technical Data

General information

Form of lens Colour of lens Diameter of collar

Dimensions Length of collar Width of collar

Overall height
Mounting depth
Mounting hole

Mechanical design

Mounting Terminals Lamp socket Lamp see order block see order block see order block

see order block see order block 1 mm 18 mm 5 mm

pressing into hole solder terminals no

filament lamp

Electrical characteristics

Voltage limit max. 24 V Power limit max. 0.45 W

Other specifications


Operating life 10,000 h
Degree of protection from IP40
front side
Weight 0.3 g

integr. Lamp

3 - 26 Signal lamps



Signal lamps with integrated filament lamp - 5 mm, round lens



Voltage limit max.	Power limit max.	Lamp	Operating life	Colour of lens	Order no.
24 V	0.45 W	filament lamp	10000 h	transparent colourless	1.69.508.113/1002
24 V	0.45 W	filament lamp	10000 h	transparent red	1.69.508.113/1301
24 V	0.45 W	filament lamp	10000 h	transparent yellow	1.69.508.113/1402
24 V	0.45 W	filament lamp	10000 h	transparent green	1.69.508.113/1502
24 V	0.45 W	filament lamp	10000 h	transparent blue	1.69.508.113/1601

Technical data see page 3 - 26

integr. Lamp