



Steatite Connectors

131 - 2 pole, conductor size up to 6 mm²



Approvals

Nominal cross-section	mm²	6,0
Voltage rating	V	450

Technical data

Connection	screw conductor size 0.5 - 6.0 mm ²
Fixing	by screw or rivet size Ø 3.7 mm
Mouldings	steatite C 220 EN 60672 continuous working temperature 1000 °C
Contacts	brass, plated continuous working temperature 350 °C
Screws	M3.5: ⌀ max. 0.8 Nm steel, zinc plated, chromed
Current rating	to EN 60598: 16 A at T 100 °C to EN 60998: 24 A at T 100 °C
Stripping length	10 - 11 mm

Upon request

4 pole, spring washers and plain washers assembled; further product variants [here](#)

Order info

Description	Item	Order No.	PU	
2 pole	131/ 2	422602	100	> ☒
4 pole	131/ 4	422604	100	> ☒