


Part Number: 1950X23X

| Type | Size | Rating | Description |
|------|------|--------|------------------------------|
| LED | M8 | 230Vac | LED Recessed Panel Indicator |

Dimensions (mm)



| Part # | Colour | Current (mA) | Intensity (mcd) |
|----------|--------|--------------|-----------------|
| 1950X230 | Red | 3 | 22 |
| 1950X231 | Green | 3 | 5 |
| 1950X232 | Yellow | 3 | 7 |

Bezel types - X=0 satin chrome / X=1 black chrome / X=2 matt chrome

Notes:

- 1 Electrical & optical data are measured at an ambient temperature of 25°C
- 2 Storage temperature -25 °C to +80°C
- 3 Application temperature -20 °C to +60°C
- 4 Due to component tolerances, colour temperature variations may be observed
- 5 The terminals are not qualified for soldering
- 6 Sealed to IP67 above panel when supplied gasket used
- 7 The plastic(polycarbonate) has limited chemical resistance
- 8 RoHS & REACH SVHC compliant