

MCN150-E

COMPACT METAL CONNECTING NAILER 38MM MAX



Diameter: 3.3 - 3.8mm
Length: 38 - 38mm

Features



Rubber Comfort Grip



Magnesium Housing



Serrated Tip



Adjustable Exhaust



Sequential Trip



Compact Magazine



Carry Case



Exposed Nail Tip



Tool Lock-Out



SPECIFICATION

Power type	Pneumatic	Operating pressure	4.80 - 8.40 BAR
Weight	1.95 kg		70.00 - 120.00 PSI
Width	86 mm	Air Consumption Ltr.per shot @ 5.6 bar	1.9
Length	296 mm	Air fitting thread type	1/4 BSP
Height	267 mm	Noise	LPA 1sd 92.70
Magazine capacity (max)	29		LWA 1sd 101.40
PT-MC Series Fasteners:			LPA 1s, 1m 88.40
Diameter (mm)	3.3 (min) 3.8 (max)	Vibration / Uncertainty	5.11 / 2.044 m/s ²
Length (mm)	38 (min) 38 (max)		
Head (mm)	7.2 (min) 7.2 (max)		
Collation type	papertape		
Collation angle	33		