




ESTGH050MSS00.5E05 (M20)

Connection technology



1: O-ring

Product characteristics

Adapter plug

M12 connector

M20 - M12

Electrical data

Electrical design

AC/DC

Operating voltage [V]

125 AC/DC

Environment

Ambient temperature [°C]

-25...85

Protection

IP 68

Mechanical data

Design

straight

Housing materials

Brass nickel-plated

Weight [kg]

0.027

Electrical connection

Connection

PVC cable / 0.5 m; 4 x 0.25 mm<sup>2</sup> + 1 x 0.5 mm<sup>2</sup>

**Wiring**

Core colours

BK black


BN brown

BU blue

GN green

WH white

YE yellow



1 BN

2 WH

3 BU

4 BK

5 GN/YE

Remarks

Pack quantity

[piece]

1